

Features

- Low Dropout Voltage: 1.15V(typ.) at 1000mA Output Current
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant. See ordering information)

Maximum Ratings

- Thermal Resistance: 100°C/W Junction to Ambient
- Storage Temperature Range: -55°C to +150°C
- Operating Junction Temperature : 150°C


Parameter	Symbol	Value	Unit
Input Voltage	V_1	20	V
ESD Voltage (Machine Model)	V_{ESD}	400	V

Recommended Operating Conditions

Parameter	Symbol	Value	Unit
Input Voltage	V_i	15	V
Operating Junction Temperature	T_j	-25 ~125	°C


Low Dropout Linear Regulator

SOT-223



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.248	0.264	6.30	6.70	
B	0.130	0.146	3.30	3.70	
C	0.264	0.287	6.70	7.30	
D	0.001	0.004	0.02	0.10	
E	0.114	0.122	2.90	3.10	
F	0.091		2.30		TYP.
G	---	0.071	---	1.80	
H	0.009	0.014	0.23	0.35	
J	0.030	---	0.75	---	
K	0.026	0.033	0.66	0.84	

Suggested Solder Pad Layout



Electrical Characteristics ($V_{in} \leq 10$, $T_J = 25^\circ\text{C}$ Unless Otherwise Specified)

Parameter	Symbol	Part Number	Test Conditions	Min	Typ	Max	Unit
Reference Voltage	V_{IROC}	MCT1117B-ADJ	$I_{OUT} = 10\text{mA}$, $V_{IN} = 3.23\text{V}$	1.231	1.25	1.269	V
			$10\text{mA} \leq I_{OUT} \leq 1\text{A}$, $2.75\text{V} \leq V_{IN} - V_{OUT} \leq 13.25\text{V}$	1.225	1.25	1.275	V
Output Voltage	V_O	MCT1117B-1.8	$I_{OUT} = 10\text{mA}$, $V_{IN} = 3.8\text{V}$	1.773	1.8	1.827	V
			$10\text{mA} \leq I_{OUT} \leq 1\text{A}$, $3.3\text{V} \leq V_{IN} \leq 12\text{V}$	1.764	1.8	1.836	V
		MCT1117B-2.5	$I_{OUT} = 10\text{mA}$, $V_{IN} = 4.5\text{V}$	2.463	2.5	2.538	V
			$10\text{mA} \leq I_{OUT} \leq 1\text{A}$, $4\text{V} \leq V_{IN} \leq 12\text{V}$	2.45	2.5	2.55	V
		MCT1117B-3.3	$I_{OUT} = 10\text{mA}$, $V_{IN} = 5.3\text{V}$	3.251	3.3	3.35	V
			$10\text{mA} \leq I_{OUT} \leq 1\text{A}$, $4.8\text{V} \leq V_{IN} \leq 12\text{V}$	3.234	3.3	3.366	V
		MCT1117B-5.0	$I_{OUT} = 10\text{mA}$, $V_{IN} = 7.0\text{V}$	4.925	5	5.075	V
			$10\text{mA} \leq I_{OUT} \leq 1\text{A}$, $6.5\text{V} \leq V_{IN} \leq 12\text{V}$	4.9	5	5.1	V
Line Regulation	LNR	MCT1117B-ADJ	$I_{OUT} = 10\text{mA}$, $1.5\text{V} \leq V_{IN} - V_{OUT} \leq 12\text{V}$	-	-	0.2	%
		MCT1117B-1.8	$I_{OUT} = 10\text{mA}$, $1.5\text{V} \leq V_{IN} - V_{OUT} \leq 10.2\text{V}$	-	-	7	mV
		MCT1117B-2.5	$I_{OUT} = 10\text{mA}$, $1.5\text{V} \leq V_{IN} - V_{OUT} \leq 9.5\text{V}$	-	-	7	mV
		MCT1117B-3.3	$I_{OUT} = 10\text{mA}$, $1.5\text{V} \leq V_{IN} - V_{OUT} \leq 8.7\text{V}$	-	-	7	mV
		MCT1117B-5.0	$I_{OUT} = 10\text{mA}$, $1.5\text{V} \leq V_{IN} - V_{OUT} \leq 7\text{V}$	-	-	10	mV
Load Regulation	LDR	MCT1117B-ADJ	$V_{IN} - V_{OUT} = 1.5\text{V}$, $10\text{mA} \leq I_{OUT} \leq 1\text{A}$	-	-	0.4	%
		MCT1117B-1.8		-	-	7.2	mV
		MCT1117B-2.5		-	-	10	mV
		MCT1117B-3.3		-	-	13.2	mV
		MCT1117B-5.0		-	-	20	mV
Dropout Voltage	V_D		$\Delta V_{REF} = 1\%$, $I_{OUT} = 1.0\text{A}$	-	-	1.3	V
Adjustment Pin Current	I_{adj}			-	60	120	μA
Minimum Load Current	I_L		$1.5\text{V} \leq V_{IN} - V_{OUT} \leq 12\text{V}$ (ADJ only)	-	1.7	5	μA
Quiescent Current	I_q		$V_{IN} = V_{OUT} + 1.25\text{V}$ (ADJ except)	-	-	10	mA
Ripple Rejection	RR		$f = 120\text{Hz}$, $C_{OUT} = 22\mu\text{F}$ Tantalum, $V_{IN} - V_{OUT} = 3\text{V}$, $I_{OUT} = 1\text{A}$	60	75	-	dB
Temperature Stability				-	0.5	-	%
Long-Term Stability			$T_A = 125^\circ\text{C}$, 1000hrs	-	0.3	-	%
RMS Output Noise (% of V_{OUT})			$T_A = 25^\circ\text{C}$, $10\text{Hz} \leq f \leq 10\text{kHz}$	-	0.003	-	%
Thermal Shutdown Hysteresis				-	25	-	$^\circ\text{C}$

Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:2.5Kpcs/Reel

Note : Adding "-HF" Suffix for Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.