




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED PER ECN-26-383793	12MAY2026	DW	SJ

D



- NOTE : UNLESS OTHERWISE SPECIFIED
- FABRICATE TO MEET IPC – 6013, CLASS 2.
INSPECT TO MEET IPC-A-600, CLASS 2.
 - CONSULT TE CONNECTIVITY DATA SHEET DS2195835
 - MATERIAL :
 - A. FPCB + ADHESIVE
 - B. ADHESIVE WITH LINER ON THER BACK SIDE, REMOVE LINER TO APPLY.
 - C. COAX CABLE : DIA.1.13, CONN. : I-PEX MHF 1/MHF 4L OR TE APPROVED EQUIVALENT
 - MINIMUM IDENTIFICATION INCLUDES
 - A: TE LOGO, TE P/N
 - B: WORD REV., FOLLOWED BY THE LASTEST REVISION LETTER. AS SHOWN.
 - C: 4 DIGITS DATE CODE: FIRST 2 DIGITS FOR THE WEEK CODE AND THE 2 DIGITS FOR THE YEAR CODE.
 - OTHERS: SPECIFIC TE INTERNAL USE ONLY.
 - GENERAL TOLERANCES : ± 0.20
 - PACKING: SECURELY SHRINK WRAPPED, VACUUM PACKED OR BAGS PACKAGED IN BULK.




MHF 4L	1.13	300 $\pm$ 3	1-2195835-4
		250 $\pm$ 3	1-2195835-3
		200 $\pm$ 2	2195835-8
		150 $\pm$ 2	2195835-7
		100 $\pm$ 2	2195835-6
MHF 1	1.13	50 $\pm$ 2	2195835-5
		300 $\pm$ 3	1-2195835-2
		250 $\pm$ 3	1-2195835-1
		200 $\pm$ 2	2195835-4
		150 $\pm$ 2	2195835-3
CONNECTOR TYPE	CABLE O.D (MM) (B)	CABLE LENGTH (MM) A	PART NUMBER

B

A

DOUBLE SIDED TAPE	ADHESIVE	3
COAX CABLE & CONNECTOR	CABLE ASSY	2
PI	FPC ANTENNA	1
MATERIAL	NAME	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DC HSIANG 19DEC2019		TE Connectivity			
DIMENSIONS: mm		CHK SHIN HOO 06JUN2020					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD AMOS CHEAH 06JUN2020		NAME FPC ANT, MHF/MHF4L, ISM 868/915MHz, HORIZONTAL -		
			PRODUCT SPEC 108-61449				
			APPLICATION SPEC -				
			WEIGHT -				
MATERIAL -	FINISH -		CUSTOMER DRAWING		SCALE 3:2	SHEET 1 OF 1	REV A3