




SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material:

- Housing: PBT Glass Filled (UL 94V-0)
- Color: Black
- Spring Wire: 0.45mm Diameter Phosphor Bronze
Gold Plating over Nickel
- Temp. Range: -40°C/+85°C
- Durability: 750 Mating cycles Min.
- Soldering Temp: 235 Deg C for 5 seconds

Electrical:


- Current rating: 1.5A Max.
- Voltage rating: 150V AC
- Insulation Resistance: 500 MΩ Min.
- Contact Resistance: 30mΩ Max.
- Dielectric Voltage: 1,000 Vrms for 60 sec. min.

● Part Number


PJ012-8P8CX

RoHS Compliant

Gold plating	1=6u" 2=15u" 3=30u" 4=50u"
--------------	-------------------------------



PCB LAYOUT
(Top View)



A(2:1)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

ON-SHORE TECHNOLOGY, INC.							
TITLE		PJ012, 8 pos, 8 cont, top entry, thru hole					
PART NO.		PJ012-8P8CX		DWG NO.		PJ012-8P8CX.DWG	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
Billy 2013.08.26		Liu 2013.08.26	Jason 2013.08.26	Steven 2013.08.26			
						UNIT: mm	X.XX ±0.25
						SCALE: NONE	X.XXX ±0.13
						X.XXXX ±0.05	
						SHEET: 01/01	REV.: A