



PRODUCT NUMBER	PITCH
YK111xx3x0J0G	11.00 mm



DIMENSION

Dim A	(N+1)×11.0+7.8
Dim B	(N-1)×11.0
Dim C	(N+1)×11.0+1

N=Number of poles

Poles	Tolerance
2p-8p	±0.20
9p-14p	±0.30
15p-20p	±0.40
21p-24p	±0.50
25p-30p	±0.60

PART NO.: YK 111xx 3 x 0 J0G

No. of poles
02 2 poles
03 3 poles
... ...
30 30 poles

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

Plated
RoHS compliant
(lead<4%)
In copper Alloy

MATERIALS & ELECTRICAL

RATED VOLTAGE & CURRENT:

300V, 20 A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

-40 °C ~ +115 °C

SCREW TORQUE VALUE:

11lb-In

WIRE RANGE:

22-12 AWG

1) HOUSING: Thermoplastic (UL 94 V-0)

BRASS, 1.2t

3) TERMINAL SCREWS: STEEL, M4

APPROVAL: cULus

mat'l. code				surface	tolerance	projection	product family
Itr	ecn	no	dr	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
				tolerances unless otherwise specified			
				angles	X.±0.5	MM	
				dr	X.X±0.3		
				engr	X.XX±0.1	scale	
				chr	HANKE FENG		
				appd	SHI JUN		
sheet	revision	A					
index	sheet	1					

