MOSFET – N-Channel, QFET®

1000 V, 1.6 A, 9 Ω


FQU2N100, FQD2N100


This N−Channel enhancement mode power MOSFET is produced using **onsemi**'s proprietary planar stripe and DMOS technology. This advanced MOSFET technology has been especially tailored to reduce on−state resistance, and to provide superior switching performance and high avalanche energy strength. These devices are suitable for switched mode power supplies, active power factor correction (PFC), and electronic lamp ballasts.

Features


- 1.6 A, 1000 V, $R_{DS(on)}$ = 9 Ω (Max.) @ V_{GS} = 10 V, I_D = 0.8 A
- Low Gate Charge (Typ. 12 nC)
- Low Crss (Typ. 5 pF)
- 100% Avalanche Tested
- These Devices are Pb−Free, Halid Free and are RoHS Compliant

V_{DSS}	$R_{DS(ON)}$ MAX	I_D MAX
1000 V	9 Ω @ 10 V	1.6 A





DPAK3 (IPAK)
CASE 369AR




DPAK3 (TO−252 3 LD)
CASE 369AS


MAXIMUM RATINGS (T_C = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain−Source Voltage	V_{DSS}	1000	V
Drain Current − Continuous (T_C = 25°C) − Continuous (T_C = 100°C)	I_D	1.6 1.0	A
Drain Current − Pulsed (Note 1)	I_{DM}	6.4	A
Gate−Source Voltage	V_{GSS}	±30	V
Single Pulsed Avalanche Energy (Note 2)	E_{AS}	160	mJ
Avalanche Current (Note 1)	I_{AR}	1.6	A
Repetitive Avalanche Energy (Note 1)	E_{AR}	5.0	mJ
Peak Diode Recovery dv/dt (Note 3)	dv/dt	5.5	V/ns
Power Dissipation (T_A = 25°C) *	P_D	2.5	W
Power Dissipation (T_C = 25°C) − Derate above 25°C		50 0.4	W W/°C
Operating and Storage Temperature Range	T_J, T_{STG}	−55 to +150	°C
Maximum Lead Temperature for Soldering Purposes, 1/8" (from case for 5 seconds)	T_L	300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

MARKING DIAGRAMS





FQU2N100,
FQD2N100 = Device Code
$Y = **onsemi** Logo
&Z = Assembly Location
&3 = 3−Digit Date Code
&K = 2−Digits Lot Run Traceability Code

ORDERING INFORMATION

Device	Package	Shipping†
FQU2N100TU	DPAK3 (IPAK) (Pb−Free)	70 Units / Tube
FQD2N100TM	DPAK3 (Pb−Free)	2500 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2004

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction−to−Case, Max.	2.5	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction−to−Ambient (minimum pad of 2 oz copper) , Max.	110	°C/W
	Thermal Resistance, Junction−to−Ambient (* 1 in2 pad of 2 oz copper), Max.	50	

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise specified)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
BV_{DSS}	Drain−to−Source Breakdown Voltage	I_D = 250 μA, V_{GS} = 0 V	1000	–	–	V
ΔBV_{DSS} / ΔT_J	Breakdown Voltage Temperature Coefficient	I_D = 250 μA, Referenced to 25°C	–	0.976	–	V/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = 1000 V, V_{GS} = 0 V	–	–	10	μA
		V_{DS} = 800 V, T_C = 125°C	–	–	100	
I_{GSSF}	Gate−Body Leakage Current, Forward	V_{GS} = 30 V, V_{DS} = 0 V	–	–	100	nA
I_{GSSR}	Gate−Body Leakage Current, Reverse	V_{GS} = −30 V, V_{DS} = 0 V	–	–	−100	nA
ON CHARACTERISTICS						
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS} = V_{GS}, I_D = 250 μA	3.0	–	5.0	V
$R_{DS(on)}$	Static Drain−Source On Resistance	V_{GS} = 10 V, I_D = 0.8 A	–	7.1	9	Ω
g_{FS}	Forward Transconductance	V_{DS} = 50 V, I_D = 0.8 A	–	1.9	–	S
DYNAMIC CHARACTERISTICS						
C_{iss}	Input Capacitance	V_{DS} = 25 V, V_{GS} = 0 V, f = 1.0 MHz	–	400	520	pF
C_{oss}	Output Capacitance		–	40	52	
C_{rss}	Reverse Transfer Capacitance		–	5	6.5	
SWITCHING CHARACTERISTICS						
$t_{d(on)}$	Turn−On Delay Time	V_{DD} = 500 V, I_D = 2.0 A, R_G = 25 Ω (Note 4)	–	13	35	ns
t_r	Turn−On Rise Time		–	30	70	
$t_{d(off)}$	Turn−Off Delay Time		–	25	60	
t_f	Turn−Off Fall Time		–	35	80	
Q_g	Total Gate Charge	V_{DS} = 800 V, I_D = 2.0 A, V_{GS} = 10 V (Note 4)	–	12	15.5	nC
Q_{gs}	Gate−Source Charge		–	2.5	–	
Q_{gd}	Gate−Drain Charge		–	6.5	–	
DRAIN−SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS						
I_S	Maximum Continuous Drain−Source Diode Forward Current		–	–	1.5	A
I_{SM}	Maximum Pulsed Drain−Source Diode Forward Current		–	–	6.0	A
V_{SD}	Drain−Source Diode Forward Voltage	V_{GS} = 0 V, I_S = 1.6 A	–	–	1.4	V
t_{rr}	Reverse Recovery Time	V_{GS} = 0 V, I_S = 2.0 A, dI_F/dt = 100 A/μs	–	520	–	ns
Q_{rr}	Reverse Recovery Charge		–	2.3	–	μC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Repetitive Rating : Pulse width limited by maximum junction temperature.
2. L = 120 mH, I_{AS} = 1.6 A, V_{DD} = 50 V, R_G = 25 Ω, Starting T_J = 25°C.
3. I_{SD} ≤ 2.0 A, di/dt ≤ 300A/μs, V_{DD} ≤ BV_{DSS}, Starting T_J = 25°C.
4. Essentially independent of operating temperature.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. On−Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On−Resistance Variation vs. Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 5. Capacitance Characteristics




Figure 6. Gate Charge Characteristics

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (continued)




Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 8. On−Resistance Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 10. Maximum Drain Current vs. Case Temperature




Figure 11. Transient Thermal Response Curve

Downloaded from Arrow.com.




Figure 12. Gate Charge Test Circuit & Waveform




Figure 13. Resistive Switching Test Circuit & Waveforms




Figure 14. Unclamped Inductive Switching Test Circuit & Waveforms

Downloaded from Arrow.com.





Figure 15. Peak Diode Recovery dv/dt Test Circuit & Waveforms

QFET is a registered trademarks of Semiconductor Components Industries, LLC dba “**onsemi**” or its affiliates and/or subsidiaries in the United States and/or other countries.

Downloaded from Arrow.com.

DPAK3 (IPAK)
CASE 369AR
ISSUE O

DATE 30 SEP 2016




NOTES: UNLESS OTHERWISE SPECIFIED

A) ALL DIMENSIONS ARE IN MILLIMETERS.
B) THIS PACKAGE CONFORMS TO JEDEC, TO−251, ISSUE C, VARIATION AA, DATED SEP 1988.
C) DIMENSIONING AND TOLERANCING PER ASME Y14.5M−1994.

DOCUMENT NUMBER:	**98AON13815G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	**DPAK3 (IPAK)**		**PAGE 1 OF 1**


onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.




DPAK3 6.10x6.54x2.29, 4.57P
CASE 369AS
ISSUE B


DATE 20 DEC 2023




NON-DIODE PRODUCTS VERSION



NON-DIODE PRODUCTS VERSION




NOTES: UNLESS OTHERWISE SPECIFIED
A) THIS PACKAGE CONFORMS TO JEDEC, TO-252, ISSUE F, VARIATION AA.
B) ALL DIMENSIONS ARE IN MILLIMETERS.
C) DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2018.
D) SUPPLIER DEPENDENT MOLD LOCKING HOLES OR CHAMFERED CORNERS OR EDGE PROTRUSION.
E) FOR DIODE PRODUCTS, L4 IS 0.25 MM MAX PLASTIC BODY STUB WITHOUT CENTER LEAD.
F) DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR EXTRUSIONS.
G) LAND PATTERN RECOMMENDATION IS BASED ON IPC7351A STD TO228P991X239-3N.



DETAIL A
(ROTATED -90°)
SCALE: 12X

DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	2.18	2.29	2.39
A1	0.00	–	0.127
b	0.64	0.77	0.89
b2	0.76	0.95	1.14
b3	5.21	5.34	5.46
c	0.45	0.53	0.61
c2	0.45	0.52	0.58
D	5.97	6.10	6.22
D1	5.21	---	---
E	6.35	6.54	6.73
E1	4.32	---	---
e	2.286 BSC		
e1	4.572 BSC		
H	9.40	9.91	10.41
L	1.40	1.59	1.78
L1	2.90 REF		
L2	0.51 BSC		
L3	0.89	1.08	1.27
L4	---	---	1.02
θ	0°	---	10°



LAND PATTERN RECOMMENDATION

*FOR ADDITIONAL INFORMATION ON OUR PB-FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ON SEMICONDUCTOR SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

XXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
ZZ = Assembly Lot Code

DOCUMENT NUMBER:	**98AON13810G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**DPAK3 6.10x6.54x2.29, 4.57P**	**PAGE 1 OF 1**

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2016

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.