



Part Number : [1205040002](#)

Product Description : Micro-Change (M12) L-Coded Solid Body Splitter, 2 x 5-Pole Female to 1 x 5-Pole Male, Black Overmold

Series Number : 120504

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Part Number : LVP5TMF-000



Documents and Resources

Drawings

[1205040002 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2022)4187-DC (10 June 2022) SCIP:52702332-ebb7-4e9a-917f-e3299eade876
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120504
Description	Micro-Change (M12) L-Coded Solid Body Splitter, 2 x 5-Pole Female to 1 x 5-Pole Male, Black Overmold
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - Solid Body
UPC	195842242654

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	63V AC/DC

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Female
Keyway	L-Coded
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female

Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PBT
Material - Coupling Nut	Nickel-plated Brass
Net Weight	113.390/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Male
Temperature Range - Operating	-25° to +85°C

This document was generated on May 26, 2026