



**Part Number :** [2132741003](#)

**Product Description :** PowerPlane Bus Bar Assembly, Vertical Mount, Dual Hole, Closed Side Walls, Silver (Ag) Plated

**Series Number :** 213274

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[2132741003\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications


[2132740001-AS-000.pdf](#)

[2132740001-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	213274
Description	PowerPlane Bus Bar Assembly, Vertical Mount, Dual Hole, Closed Side Walls, Silver (Ag) Plated
Application	Power
Component Type	PCB Receptacle
Product Name	PowerPlane
UPC	195842284487

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	320.0A
Voltage - Maximum	1000V

### Physical

Circuits (Loaded)	1
Circuits (maximum)	1

Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Nickel
Material - Resin	Polyester
Net Weight	19.824/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw

---

This document was generated on May 05, 2026