

ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and onsemi. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

NTMFD4C85N

PowerPhase, Dual N-Channel SO8FL

30 V, High Side 25 A / Low Side 49 A

Features

- Co-Packaged Power Stage Solution to Minimize Board Space
- Minimized Parasitic Inductances
- Optimized Devices to Reduce Power Losses
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- DC-DC Converters
- System Voltage Rails
- Point of Load




Figure 1. Typical Application Circuit





Figure 2. Typical Efficiency Performance
POWERPHASEGEVB Evaluation Board




ON Semiconductor®

www.onsemi.com


$V_{(BR)DSS}$	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
Q1 Top FET 30 V	3.0 mΩ @ 10 V	25 A
	4.3 mΩ @ 4.5 V	
Q2 Bottom FET 30 V	0.8 mΩ @ 10 V	49 A
	1.2 mΩ @ 4.5 V	




PIN CONNECTIONS



MARKING DIAGRAM



DFN8
CASE 506CR



4C85N = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 11 of this data sheet.

NTMFD4C85N

Table 1. MAXIMUM RATINGS (T_J=25°C unless otherwise stated)

Parameter				Symbol	Value	Units
Drain-to-Source Voltage			Q1	V _{DSS}	30	V
			Q2			
Gate-to-Source Voltage			Q1	V _{GS}	±20	V
			Q2			
Continuous Drain Current R _{θJA} (Note 1)	Steady State	T _A = 25°C	Q1	I _D	20.1	A
		T _A = 85°C			14.5	
		T _A = 25°C	Q2		39	
		T _A = 85°C			28.1	
Power Dissipation R _{θJA} (Note 1)		T _A = 25°C	Q1	P _D	1.95	W
			Q2			
Continuous Drain Current R _{θJA} ≤ 10 s (Note 1)		T _A = 25°C	Q1	I _D	25.4	A
					T _A = 85°C	
		T _A = 25°C	Q2		49.2	
					T _A = 85°C	
Power Dissipation R _{θJA} ≤ 10 s (Note 1)		T _A = 25°C	Q1	P _D	3.10	W
			Q2			
Continuous Drain Current R _{θJA} (Note 2)		T _A = 25°C	Q1	I _D	15.4	A
					T _A = 85°C	
		T _A = 25°C	Q2		29.7	
					T _A = 85°C	
Power Dissipation R _{θJA} (Note 2)	T _A = 25°C	Q1	P _D	1.13	W	
		Q2				
Continuous Drain Current R _{θJC}	T _C = 25°C	Q1	I _D	67	A	
		Q2		174		
Power Dissipation R _{θJC}		Q1	P _D	22	W	
				Q2		40
Pulsed Drain Current		T _A = 25°C t _p = 10 μs	Q1	I _{DM}	300	A
			Q2		525	
Operating Junction and Storage Temperature			Q1	T _J , T _{STG}	−55 to +150	°C
			Q2			
Source Current (Body Diode)			Q1	I _S	10	A
			Q2		10	
Drain to Source DV/DT				dV/dt	6	V/ns
Single Pulse Drain-to-Source Avalanche Energy (T _J = 25°C, V _{DD} = 50 V, V _{GS} = 10 V, L = 0.1 mH, R _G = 25 Ω)		I _L = 19 A _{pk}	Q1	EAS	34.5	mJ
		I _L = 26 A _{pk}	Q2	EAS	222	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)				T _L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using 1 sq-in pad, 2 oz Cu.
2. Surface-mounted on FR4 board using the minimum recommended pad size of 100 mm².

NTMFD4C85N

Table 2. THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Units
Junction-to-Ambient – Steady State (Note 3)	$R_{\theta JA}$	64.2	$^{\circ}\text{C/W}$
Junction-to-Ambient – Steady State (Note 4)		110.5	
Junction-to-Ambient – ($t \leq 10$ s) (Note 3)		40.3	
Junction-to-Case (bottom) – Steady State Q1	$R_{\theta JC}$	5.6	$^{\circ}\text{C/W}$
Junction-to-Case (bottom) – Steady State Q2		3.1	

3. Surface-mounted on FR4 board using 1 sq-in pad, 2 oz Cu

4. Surface-mounted on FR4 board using the minimum recommended pad size of 100 mm²

Table 3. ELECTRICAL CHARACTERISTICS ($T_J = 25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	FET	Test Condition	Min	Typ	Max	Units
OFF CHARACTERISTICS							
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	Q1	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	30			V
		Q2		30			
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS} / T_J$	Q1			19		mV/ $^{\circ}\text{C}$
		Q2			17		
Zero Gate Voltage Drain Current	I_{DSS}	Q1	$V_{GS} = 0 \text{ V}, V_{DS} = 24 \text{ V}$			1	μA
						10	
		Q2				1	
Gate-to-Source Leakage Current	I_{GSS}	Q1	$V_{DS} = 0 \text{ V}, V_{GS} = 20 \text{ V}$			100	nA
		Q2				100	

ON CHARACTERISTICS (Note 5)

Gate Threshold Voltage	V _{GS(TH)}	Q1	V _{GS} = V _{DS} , I _D = 250 μA		1.3		2.1	V
		Q2			1.3		2.1	
Negative Threshold Temperature Coefficient	V _{GS(TH)} / T _J	Q1				4.3		mV/°C
		Q2				4.6		
Drain-to-Source On Resistance	R _{DS(on)}	Q1	V _{GS} = 10 V	I _D = 20 A		2.2	3.0	mΩ
			V _{GS} = 4.5 V	I _D = 20 A		3.3	4.3	
		Q2	V _{GS} = 10 V	I _D = 30 A		0.6	0.8	
			V _{GS} = 4.5 V	I _D = 30 A		0.95	1.2	

CAPACITANCES

Input Capacitance	C_{ISS}	Q1	$V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}, V_{DS} = 15 \text{ V}$		1960		pF
		Q2			6660		
Output Capacitance	C_{OSS}	Q1			1230		
		Q2			3660		
Reverse Capacitance	C_{RSS}	Q1			102		
		Q2			126		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width $\leq 300 \mu\text{s}$, duty cycle $\leq 2\%$

6. Switching characteristics are independent of operating junction temperatures

NTMFD4C85N

Table 3. ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	FET	Test Condition	Min	Typ	Max	Units
CHARGES & GATE RESISTANCE							
Total Gate Charge	$Q_{G(TOT)}$	Q1	$V_{GS} = 4.5\text{ V}, V_{DS} = 15\text{ V}; I_D = 20\text{ A}$		15		nC
		Q2			45.2		
Threshold Gate Charge	$Q_{G(TH)}$	Q1			1.5		
		Q2			4.5		
Gate-to-Source Charge	Q_{GS}	Q1			5.0		
		Q2			15		
Gate-to-Drain Charge	Q_{GD}	Q1			5.2		
		Q2			11.8		
Total Gate Charge	$Q_{G(TOT)}$	Q1	$V_{GS} = 10\text{ V}, V_{DS} = 15\text{ V}; I_D = 20\text{ A}$		32		nC
		Q2			99.3		
Gate Resistance	R_G	Q1	$T_A = 25^\circ\text{C}$		1.0		Ω
		Q2			1.0		

SWITCHING CHARACTERISTICS (Note 6)

Turn-On Delay Time	$t_{d(ON)}$	Q1	$V_{GS} = 4.5\text{ V}, V_{DS} = 15\text{ V}, I_D = 20\text{ A}, R_G = 3.0\ \Omega$		10.3		ns
		Q2			19.5		
Rise Time	t_r	Q1			37		
		Q2			27		
Turn-Off Delay Time	$t_{d(OFF)}$	Q1			20		
		Q2			47		
Fall Time	t_f	Q1			5.6		
		Q2			15		

SWITCHING CHARACTERISTICS (Note 6)

Turn-On Delay Time	$t_{d(ON)}$	Q1	$V_{GS} = 10\text{ V}, V_{DS} = 15\text{ V}, I_D = 20\text{ A}, R_G = 3.0\ \Omega$		8.0		ns
		Q2			12.6		
Rise Time	t_r	Q1			31.5		
		Q2			22.7		
Turn-Off Delay Time	$t_{d(OFF)}$	Q1			25		
		Q2			60		
Fall Time	t_f	Q1			4.0		
		Q2			12.2		

DRAIN-SOURCE DIODE CHARACTERISTICS

Forward Voltage	V_{SD}	Q1	$V_{GS} = 0\text{ V}, I_S = 10\text{ A}$	$T_J = 25^\circ\text{C}$		0.78	V
				$T_J = 125^\circ\text{C}$		0.62	
		Q2	$V_{GS} = 0\text{ V}, I_S = 10\text{ A}$	$T_J = 25^\circ\text{C}$		0.75	
				$T_J = 125^\circ\text{C}$		0.55	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width $\leq 300\ \mu\text{s}$, duty cycle $\leq 2\%$

6. Switching characteristics are independent of operating junction temperatures

NTMFD4C85N

Table 3. ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	FET	Test Condition	Min	Typ	Max	Units
DRAIN-SOURCE DIODE CHARACTERISTICS							
Reverse Recovery Time	t_{RR}	Q1	$V_{GS} = 0\text{ V}, dI_S/dt = 100\text{ A}/\mu\text{s},$ $I_S = 2\text{ A}$		40		ns
		Q2			73		
Charge Time	t_a	Q1			20		
		Q2			40		
Discharge Time	t_b	Q1			20		
		Q2			33		
Reverse Recovery Charge	Q_{RR}	Q1			37		nC
		Q2			137		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$

6. Switching characteristics are independent of operating junction temperatures

TYPICAL CHARACTERISTICS – Q1




Figure 3. On-Region Characteristics




Figure 4. Transfer Characteristics




Figure 5. On-Resistance vs. Gate-to-Source Voltage




Figure 6. On-Resistance vs. Drain Current and Gate Voltage




Figure 7. On-Resistance Variation with Temperature




Figure 8. Capacitance Variation

TYPICAL CHARACTERISTICS – Q1




Figure 9. On-Region Characteristics




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 12. Drain-to-Source Leakage Current vs. Voltage




Figure 13. Maximum Rated Forward Biased Safe Operating Area

NTMFD4C85N

TYPICAL CHARACTERISTICS – Q1




Figure 14. Thermal Characteristics

TYPICAL CHARACTERISTICS – Q2




Figure 15. On-Region Characteristics




Figure 16. Transfer Characteristics




Figure 17. On-Resistance vs. Gate-to-Source Voltage




Figure 18. On-Resistance vs. Drain Current and Gate Voltage




Figure 19. On-Resistance Variation with Temperature




Figure 20. Capacitance Variation

TYPICAL CHARACTERISTICS – Q2




Figure 21. On-Region Characteristics




Figure 22. Diode Forward Voltage vs. Current




Figure 23. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 24. Drain-to-Source Leakage Current vs. Voltage




Figure 25. Maximum Rated Forward Biased Safe Operating Area

NTMFD4C85N

TYPICAL CHARACTERISTICS – Q2




Figure 26. Thermal Characteristics

Ordering Information


Device	Package	Shipping [†]
NTMFD4C85NT1G	DFN8 (Pb-Free)	1500 / Tape & Reel
NTMFD4C85NT3G	DFN8 (Pb-Free)	5000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NTMFD4C85N

PACKAGE DIMENSIONS



DFN8 5x6, 1.27P PowerPhase FET CASE 506CR ISSUE C




NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSIONS b AND b1 APPLY TO PLATED TERMINAL AND ARE MEASURED BETWEEN 0.15 AND 0.25 MM FROM THE TIPS.
4. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
5. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
6. SEATING PLANE IS DEFINED BY THE TERMINALS. A1 IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

DIM	MILLIMETERS	
	MIN	MAX
A	0.90	1.10
A1	0.00	0.05
b	0.40	0.60
b2	0.40	0.60
c	0.20	0.30
D	5.15 BSC	
D1	4.90	5.10
D2	3.70	3.90
D3	2.96	3.16
E	6.15 BSC	
E1	5.80	6.00
E2	2.37	2.57
E3	1.05	1.25
E4	1.36	1.56
e	1.27 BSC	
G	0.625 BSC	
G1	1.615 BSC	
h	12 °	
L	0.34	0.59
L2	1.68	1.93



RECOMMENDED SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and the  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative