



Part Number : [1708142009](#)

Product Description : NeoScale High-Speed Mezzanine Receptacle, 2.80mm Pitch, 6x20, 120 Triads-100 Ohm (360 Circuits), 8.00mm Connector Height

Series Number : 170814

Status : Active

Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[1708142009 sd.pdf](#)

[PK-170814-002-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[1708072126-000.pdf](#)

[SP-170807-2005-001.zip](#)


[SP-170814-0025-001.zip](#)

Specifications

[PS-170807-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	170814
Description	NeoScale High-Speed Mezzanine Receptacle, 2.80mm Pitch, 6x20, 120 Triads-100 Ohm (360 Circuits), 8.00mm Connector Height
Application	Board-to-Board, Signal, Mezzanine
Component Type	Receptacle
Product Name	NeoScale
UPC	887191540788

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	1.0A
Grounding to PCB	No
Voltage - Maximum	30V AC (RMS)

Physical

Circuits (Loaded)	360
Circuits (maximum)	360
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	16.426/g
Number of Rows	6
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	2.80mm
Pitch - Termination Interface	2.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Solder or Weld

This document was generated on Apr 30, 2026