

- ***Height:*** *2.0mm Max*
- ***Footprint:*** *6mm x 5.4mm Max*
- ***Current Rating:*** *up to 43.0A*
- ***Inductance Range:*** *0.15uH to 68.0uH*
- *Shielded construction and compact design*
- *High current, low DCR, and high efficiency*
- *Minimized acoustic noise and minimized leakage flux*
- *40 Vdc Voltage Rating between terminals*

Electrical Specifications @ 25°C - Operating Temperature -55°C to +125°C						
Commercial[6,7]	Automotive[6,7]	Inductance[5] 100KHz, 1V	Rated[3] Current	DC Resistance		Saturation[2] Current
				TYP.	MAX.	
		uH±20%	A	mΩ	mΩ	A
PA4345.101NLT	PM4345.101NLT	**0.10***	**18.0**	**3.6**	**4.0**	**45.0**
PA4345.121NLT	PM4345.121NLT	0.12*	17.0	3.7	4.3	35.0
PA4345.151NLT	PM4345.151NLT	**0.15***	**16.0**	**3.8**	**4.6**	**27.0**
PA4345.221NLT	PM4345.221NLT	**0.22**	**15.0**	**4.0**	**5.5**	**25.0**
PA4345.241NLT	PM4345.241NLT	**0.24**	**13.0**	**6.0**	**7.0**	**23.0**
PA4345.331NLT	PM4345.331NLT	**0.33**	**12.0**	**6.3**	**7.3**	**21.3**
PA4345.361NLT	PM4345.361NLT	0.36	11.8	6.8	7.8	20.0
PA4345.471NLT	PM4345.471NLT	**0.47**	**11.5**	**7.3**	**8.6**	**18.0**
PA4345.561NLT	PM4345.561NLT	0.56	10.7	9.3	11.2	15.0
PA4345.681NLT	PM4345.681NLT	**0.68**	**10.0**	**11.0**	**12.4**	**12.8**
PA4345.821NLT	PM4345.821NLT	0.82	8.5	15.0	18.0	14.0
PA4345.102NLT	PM4345.102NLT	**1.0**	**7.0**	**17.5**	**20.0**	**13.7**
PA4345.122NLT	PM4345.122NLT	**1.2**	**6.2**	**23.0**	**28.0**	**11.0**
PA4345.152NLT	PM4345.152NLT	**1.5**	**5.5**	**26.5**	**30.5**	**9.8**
PA4345.222NLT	PM4345.222NLT	2.2	4.2	42.0	50.0	9.0
PA4345.272NLT	PM4345.272NLT	2.7	4.0	50.0	58.0	8.2
PA4345.332NLT	PM4345.332NLT	**3.3**	**3.3**	**66.0**	**76.0**	**7.3**
PA4345.472NLT	PM4345.472NLT	**4.7**	**2.8**	**103**	**116**	**5.0**
PA4345.562NLT	PM4345.562NLT	5.6	2.5	112	122	4
PA4345.682NLT	PM4345.682NLT	6.8	2.4	130	150	3.8

Downloaded from Arrow.com.


Electrical Specifications @ 25°C - Operating Temperature -55°C to +125°C						
Commercial[6,7]	Automotive[6,7]	Inductance[5] 100KHz, 1V	Rated[3] Current	DC Resistance		Saturation[2] Current
				TYP.	MAX.	
		(uH ±20%)	A	mΩ	mΩ	A
PA4345.822NLT	PM4345.822NLT	8.2	2.3	148	171	3.5
PA4345.103NLT	PM4345.103NLT	10	2.3	180	199	3.4
PA4345.153NLT	PM4345.153NLT	15	1.9	240	270	2.8
PA4345.223NLT	PM4345.223NLT	22	1.5	350	390	1.8

Notes:


1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
2. The saturation current is the current at which the initial inductance drops approximately 30% at the stated ambient temperature. This current is determined by placing the compnent in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effect) to the component.
3. The rated current is the DC current required to raise the component temperature by approximately 40˚C. Take note that the components' performanc varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
4. The part temperature (ambient+temp rise) should not exceed 125˚C under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
5. Please note that the inductance tolerance of all parts are +/-20% except those indicated with a * which are +/-30%.
6. Parts shown in bold are standard catalog parts and are available through sample stock and distribution. Parts in lighter font are available but are not necessarily held in sample stock or distribution and lead times may be longer. Please contact Pulse for availablity.
7. The PM part numbers have full automotive IATF16949 certification. The PM part number dimensions are 100% tested in production but do not necessarily meet a product capability index (Cpk) > 1.33 and therefore may not strictly conform to PPAP.
8. Special characteristics

Mechanical

PA4345/PM4345



Final Layout




SUGGESTED PAD LAYOUT

Series	A	B	C	D	E	F	G	H
PA4345/PM4345	6.0 Max	5.4 Max	2.0 Max	(2.5)	(1.1)	(2.8)	(2.0)	(2.2)

All Dimensions in mm.

Downloaded from Arrow.com.


TAPE & REEL INFO





SURFACE MOUNTING TYPE, REEL/TAPE LIST						
	REEL SIZE (mm)		TAPE SIZE (mm)			QTY
	A	G	P_1	W	K_0	PCS/REEL
PA4345/PM4345	Ø330	12	8	12	2.3	3000


Typical Performance Curves


PA4345.XXXNLT and PM4345.XXXNLT


























Downloaded from Arrow.com.






































For More Information:

Americas - prodinfo_power_americas@yageo.com | **Europe -** prodinfo_power_emea@yageo.com | **Asia -** prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2026. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

Downloaded from Arrow.com.