Part Number : 2188470001
Product Description : Universal Serial Bus (USB) Shielded I/O Plug, Type C, Vertical, Surface Mount, 24 Circuits, Gold (Au) Flash Plating
Series Number : 218847
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

2188470001_sd.pdf

2188470001PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

1054440001-000.pdf

2188470001TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	218847
Description	Universal Serial Bus (USB) Shielded I/O Plug, Type C, Vertical, Surface Mount, 24 Circuits, Gold (Au) Flash Plating
Application	Wire-to-Board
Component Type	Plug
Product Name	USB
Standard	USB 3.2 Gen 1
Type	C
UPC	196823223143

Electrical

Current - Maximum per Contact	0.25A,1.25A,5.0A, See Product Specification
Grounding to Panel	None
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	30V AC/DC

Downloaded from Arrow.com.

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Male
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Vertical
Net Weight	0.525/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	0.80mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.025µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	USB Type C Receptacle

Downloaded from Arrow.com.

Downloaded from Arrow.com.