





PRODUCT NUMBER	PITCH
VFxx72x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item **a** Short pin: Copper, Tin plated
- Item **b** Long pin: Copper, Tin plated
- Item **c** With flange nut: brass M2.5
- Item **d** Terminal (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 

Dimension	
Dim L	$(N/2+2) \times 5.0$
Dim B	$(N/2-1) \times 5.0$
Dim C	$(N/2-1) \times 5.0$
Dim D	$(N/2-1) \times 5.0 + 10.0$
Dim E	$(N/2-1) \times 5.0$
Dim F	$(N/2-1) \times 5.0 + 5.4$
Dim G	$(N/2-1) \times 5.0 + 5.4$
Dim H	$(N/2-1) \times 5.0 + 10.0$

Poles	Tolerance
2×2P-2×5P	±0.15
2×6P-2×10P	±0.20
2×11P-2×15P	±0.25
2×16P-2×20P	±0.30
2×21P-2×24P	±0.40

		Color	RoHS compliant
Solid block	0	Black (RAL9005)	(lead<4%)
No. of poles	2	Red (RAL3001/D)	In copper Alloy
04 2x2poles	3	Orange(RAL2011/P)	
06 2x3poles	4	Yellow(RAL1018/A)	
... ..	5	Green(RAL6018/T)	
48 2x24poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

[illegible]