

© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP(ECN-23-233111)	28SEP2023	ED	WH





NOTES:

1 PACK IN ACCORDANCE WITH TE SPEC 107-3275;

2 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED;

3 ELECTRICAL CHARACTERISTICS :
FREQUENCY RANGE : DC-18GHz
NOMINAL IMPEDANCE : 50 OHMS
POWER RATING: 2W
VSWR : 1.3 MAX(DC-18GHz)

4 MECHANICAL CHARACTERISTICS :
DURABILITY : 500 CYCLES
TORQUE SETTING : 7-10 IN-LBS;

5 TEMPERATURE RANGE: -40°-+125°;

6 RoHS: COMPLIANT.

	QUANTITY PER ASSY	PLATING	MATERIAL	DESCRIPTION	ITEM
	1	RED	SILICONE RUBBER	GASKET	6
	1	GOLD 1u"/ NICKEL/COPPER	BRASS	SHELL	5
	1	NATURAL	RE0603D	CHIP RESISTOR	4
	1	GOLD 10u"/ NICKEL/COPPER	BRASS	CENTER CONTACT	3
	1	NATURAL	PTFE	INSULATOR	2
	1	GOLD 1u"/ NICKEL/COPPER	BRASS	BODY	1
	2467938-1	PLATING	MATERIAL	DESCRIPTION	ITEM

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.3
1 PLC ± 0.2
2 PLC ± 0.1
3 PLC ± –
4 PLC ± –
ANGLES ± 5'

MATERIAL: SEE TABLE

FINISH: –

DWN ED 28SEP2023
CHK ED 28SEP2023
APVD WH 28SEP2023
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME: SMA MALE LOAD,CHIP RESISTOR, STRAIGHT,18GHZ
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2467938	—

CUSTOMER DRAWING

SCALE	SHEET	REV
8:1	1 OF 1	A

2467938

1471-9 (1/15)

Downloaded from Arrow.com.