

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECO-15-010090	16JUL2015	AP	DG





△1 MATERIAL:
FRONT INSULATOR: PBT, 30 %GF, UL94V-0, BLACK COLOR
BACK INSULATOR: PBT, 30 %GF, UL94V-0, BLACK COLOR
CONTACT: BRASS
FRONT & BACK SHELL: STEEL
CLINCH NUTS: BRASS

△2 FINISH:
CONTACT: GOLD PLATING 0.00002[.0000008] MIN ON CONTACT AREA 0.00229 [.000090] MIN TIN-LEAD PLATING ALL OVER 0.00127[.000050] MIN NICKEL

△3 CONTACT: GOLD PLATING 0.00076[.000030] MIN ON CONTACT AREA 0.00229 [.000090] MIN TIN-LEAD PLATING ALL OVER 0.00127[.000050] MIN NICKEL

△4 SHELL: BRIGHT TIN 0.00241[.000095] MIN FULL SHELL

△5 SHELL: BLUE ZINC: 0.00508[.000200] - 0.00762[.000300] OVER ENTIRE SHELL

△6 CONTACT: GOLD PLATING 0.00002[.0000008] MIN ON CONTACT AREA 0.00229 [.000090] MIN HOT DIPPED TIN-COPPER PLATING ALL OVER 0.00127[.000050] MIN NICKEL

△7 CLINCH NUTS: NICKEL PLATING .00305-.00508[.000120-.000200]

8 SPECIFICATION
ELECTRICAL CHARACTERISTICS: CURRENT RATING: 3 AMPERES
DIELECTRIC WITHSTANDING VOLTAGE: AC 1000V r.m.s
INSULATION RESISTANCE: 5000 MEGOHMS MINIMUM AT DC 500V
CONTACT RESISTANCE: 10 MILLIOHMS MAXIMUM.

△9 ROHS 2002/95/EC COMPLIANT

10 PLUG ASSEMBLY MATES WITH ANY 15 POSITION RECEPTACLE IN AMPLIMITE SERIES

11 SOLDER CUP WILL ACCOMMODATE 20 MAX AWG WIRE.

△12 CONTACT: GOLD PLATING 0.00076[.000030] MIN ON CONTACT AREA 0.00229[.000090] MIN HOT DIPPED TIN-COPPER ALL OVER 0.00127[.000050] MIN NICKEL PLATING

△13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	PACKAGING TYPE	CLINCH △7 NUTS	GROUNDING INDENTS	CONTACTS	SHELLS	PART NO.
△9 OBSOLETE	STANDARD	NO	NO	△6	△5	5-747908-4
△9 △13 OBSOLETE	STANDARD	YES	YES	△6	△4	~~5-747908-8~~
△9	STANDARD	NO	YES	△12	△4	5-747908-5
△9	STANDARD	NO	YES	△6	△4	5-747908-2
△9 OBSOLETE	STANDARD	NO	YES	△6	△4	747908-9
SUPERSEDED TO 5-747908-8	STANDARD	YES	YES	△2	△4	747908-8
SUPERSEDED TO 5-747908-5	STANDARD	NO	YES	△3	△4	747908-5
SUPERSEDED TO 5-747908-4	STANDARD	NO	NO	△2	△5	747908-4
SUPERSEDED TO 5-747908-2	STANDARD	NO	YES	△2	△4	747908-2

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± 0.25
2 PLC ± 0.13
3 PLC ± 0.05
4 PLC ± -
ANGLES ± 4°

MATERIAL △1
FINISH SEE TABLE

DWN	M.BINNER	03MAR03
CHK	R.BENDORF	05MAR03
APVD	R.BENDORF	05MAR03
PRODUCT SPEC	—	
APPLICATION SPEC	—	
WEIGHT	—	

TE Connectivity

NAME
PLUG ASSEMBLY, SOLDER CUP, SIZE 2, 15 POSN, HD-20, AMPLIMITE
—

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-747908	—

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV AA

747908

1471-9 (3/11)

Downloaded from Arrow.com.