
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – TE Connectivity ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G1	REVISED PER ECR-17-009545	04AUG2017	AS	RS



1. COPPER ALLOY.
2. TIN-LEAD PLATE PER ASTM-B-545, 2.54μm [.000100] MIN THICKNESS, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.
3. TIN PLATE PER ASTM-B-545, 2.54μm [.000100] MIN THICKNESS, WITH SUPPLEMENTAL ANTI FRETTING LUBRICANT.

SUPERCEDED BY 9-331256-0		9-331256-1
	3	9-331256-0
	3	1-331256-4
	–	1-331256-0
OBSOLETE	1	331256
	2	
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL 1

FINISH 2 3

DWN M. SNEED 24SEP82
CHK D. SMITH 12OCT82
APVD M. SNEED 12OCT82
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT 0.000000

TE Connectivity

NAME FERRULE, STEPDOWN

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-331256	—

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV G1

Downloaded from Arrow.com.