

Technical data sheet

Article number:
712-10002

HTAPE-PROTECT180

Product Group	Wire Harness Tape – Hand-tearable Cloth Tape
Product Family	HelaTape Protect 180
Material	Polyester (PET)
Colour	Black (BK)
Adhesion to Backing	3.0 N/10 mm
Adhesion to Steel	3.0 N/10 mm
Breaking Strength	65 N/10 mm
Elongation at break	15 %
Length (L)	25 m
Operating Temperature	-40 °C to +125 °C
Package Content packed in	reel
Pack Cont.	1 Reel
Shelf Life	24 months
Storage Temperature	+23 °C
Tensile Strength	65 N/mm ²
Thickness (T)	0.18 mm
Width (W)	19 mm

HF ✓

RoHS ✓