


Series
DSXNON ENVIRONMENTAL SIZE 5 CRIMP COAX SOCKET CONTACT
FOR RG174, RG179, RG188, RG316, KX22, FILOTEX ET 122715, ASNE 0690 CABLESIssue:
Sept. 18, 2014Page
1/1

MATERIAL :

OUTER CONTACT : BERYLLIUM COPPER PER ASTM-B-196
INSULATOR : PTFE PER ASTM-D-1710 OR EQUIVALENT
CENTER CONTACT AND FERRULE : BRASS PER ASTM B 16 OR ASTM B 453 OR EN 12164
CRIMP BARREL: BRASS PER ASTM B 16 OR ASTM B 453 OR EN 12164

FINISH:

ALL METALIC PARTS: .00005 OF GOLD PER SAE AMS-2422 OVER NICKEL PER AMS 2403


DESIGN REQUIREMENTS

TEMPERATURE RANGE: -65°C to +125°C
IMPEDANCE : 50 OHMS NOMINALE
DIELECTRIC WITHSTANDING VOLTAGE: 750 V rms AT SEA LEVEL
VSWR: 1.3 from DC TO 1500 MHz

EXTRACTION TOOL: RADIAL 282 946 (M81659/28-01) (MUST BE ORDER SEPARATLY)

WIRING INSTRUCTIONS PER : RP 7575

DIMENSIONS : mm (inch are given for information only)



Estimated weight : 4.00 g

CREATION

PEN:

NOM: FALETTI

DATE: Nov. 91,

APPR.:

Sept. 18, 14	Ø7.05/6.95 on 2 mm min -> on 3mm max	Branjonneau	Dupuis	
Sept. 12, 14	Dim body updated : add Ø7.05/6.95 on 2 mm	Moutault	Dupuis	
SEP 24 09	REDRAWN - SUPPRESS DETAIL OF WIRING INSTRUCTION UPDATED - ADDED WIRING INSTRUCTION RP7575	VALGRESY	BROCHET	
Issue	Revisions	Name	Approved	

616022EN

RADIAL PROPRIETARY INFORMATION