




STRIPPING DIMENSIONS



ASSEMBLY TOOLING:

1. CENTER CONTACT: SOLDERED
2. OUTER CONTACT: 360X10519X
USER CRIMP TOOL: 360X11019X
INSERT CAVITY A: HEX 4,52 / .178

Part no.	Finish Pos.1	Finish Pos.2	Finish Pos.3	Finish Pos. 4/5
131J20039X	min. 50µin HARD GOLD over min. 50µin NICKEL	min. 30µin HARD GOLD over min. 50µin NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL
131A20039X	GOLD FLASH over NICKEL	GOLD FLASH over NICKEL	NICKEL PLATED	GOLD FLASH over NICKEL

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance			dim. in mm
rev.	description	date	name	date	name		
				drawn	05.10.10	Henneboel	
				appd.	05.10.10	Koch	
				norm			
				d-old			
a	Origin						

scale:		8:1	
material:		see table	
title:			
COAXIAL CONTACT PLUG 50 OHM			
inner + outer conductor for crimp termination			
for cable 180 B/U			
dwg no:		Inventor 10	DIN-A3
13K2A026A		sh: 1	
part no:		see table	