




Part Number : [757830337](#)

Product Description : iPass I/O Surface Mount Receptacle, 0.80mm Pitch, Right-Angle, Internal Assembly with Shell, 68 Circuit, 0.38µm Gold (Au), Through-Hole Shell Option, Tail Length 2.79mm, Left Key

Series Number : 75783

Status : Not Recommended For New Design

Product Category : High-Speed I/O Connectors



Documents & Resources

Drawings

[757830337_sd.pdf](#)

[PK-75783-002-001.pdf](#)

[EE-75586-001-001.pdf](#)

[SP-75586-001-001.zip](#)

Specifications

[AS-75783-001-001.pdf](#)

[PS-75783-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	High-Speed I/O Connectors
Series	75783
Description	iPass I/O Surface Mount Receptacle, 0.80mm Pitch, Right-Angle, Internal Assembly with Shell, 68 Circuit, 0.38µm Gold (Au), Through-Hole Shell Option, Tail Length 2.79mm, Left Key
Application	Wire-to-Board
Comments	Positive or passive latching cable available
Component Type	Receptacle
Product Name	iPass,Mini Multi-Lane,PCI Express
Type	N/A
UPC	800756839776

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.5A
-------------------------------	------

Grounding to Panel	None
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	68
Circuits (maximum)	68
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper-Nickel-Zinc, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	4.764/g
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
PC Tail Length	2.79mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A

Wire Size (AWG)	N/A
-----------------	-----

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Use with Part(s)

Description	Part Number
iPass Cable Assemblies	<u>74573</u>
Internal iPass Mini SAS Double-Ended Plugs	<u>79576</u>

This document was generated on Sep 16, 2025