


TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 75 PCS

① PROOF OF PROCESS CAPABILITY OR 100% TEST IF
PROCESS CAPABILITY IS NOT ACHIEVED


(12) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

(7) PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3




CONSIDER MOUNTING POSITION: PEG RIGHT






PIN 1

REEL OFF DIRECTION



PCB-LAYOUT PROPOSAL



SCALE 2:1
3D VIEW

1. DRAWING SPECIFICATION ACCORDING TO
DOCUMENT 5_3-16-DOC-1806-00915

2. COPLANARITY OF ALL CLIPS $\leq 0.1\text{MM}$

 PART; 100 PCS. IN BUBBLE BAGS/BULK

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11AUG2023 N K NIKHIL CHK 13AUG2023 M SZEJAG APVD 13AUG2023 J DE BRULIN		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-1: 1989m ISO 8015		NAME M12 MALE, A CODE, 4P, 10.5MM SMT V * - -	
		PRODUCT SPEC 108-94887 APPLICATION SPEC 114-94781			
MATERIAL - -		FINISH -		SIZE A2	CAGE CODE 00779
		WEIGHT -		DRAWING NO C=484790-E	
CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1
				REV G1	