


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		B1	REVISED PER ECO-14-018035	11MAR2015	AP	DD
			B2	REVISED PER ECN-24-252171	22FEB2024	AP	RS

1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.





2 FINISH:
30µ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.

3. CONNECTORS SUPPLIED WITH MOUNTING SCREW.



SCALE 4:1

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY



RECOMMENDED PCB LAYOUT
MIN BOARD THICKNESS 1.0

KEY POSITION CHART	
	NONE
	A
	B
	C
	D
	E
	F
	G
	H

OBSOLETE	H	2	8-2132499-1
	G	2	7-2132499-1
	F	2	6-2132499-1
	E	2	5-2132499-1
	D	2	4-2132499-1
	C	2	3-2132499-1
	B	2	2-2132499-1
	A	2	1-2132499-1
NONE		2	2132499-1
KEY POSITION		FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 04FEB2011	TE Connectivity	
DIMENSIONS:		CHK D. DIXON 04FEB2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. DIXON 04FEB2011	NAME	
	0 PLC ±0.2	PRODUCT SPEC	IMPACT, 3 PAIR, DAUGHTERCARD 6 COLUMN, RIGHT GUIDED, SIGNAL MODULE, 0.39 EYELET	
	1 PLC ±0.13	APPLICATION SPEC		
	2 PLC ±0.13	WEIGHT	A100779C=2132499	
	3 PLC ±0.13	CUSTOMER DRAWING	SCALE 6:1 SHEET 1 OF 1 REV B2	
	4 PLC ±0.13			
	ANGLES ±0.13			
	FINISH SEE TABLE			