

# Power MOSFET

TO-247AC




N-Channel MOSFET

## FEATURES

- Dynamic dV/dt rating
- Repetitive avalanche rated
- Isolated central mounting hole
- Fast switching
- Ease of paralleling
- Simple drive requirements
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Available

RoHS* Available

**Note**

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details

## DESCRIPTION

Third generation Power MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The TO-247AC package is preferred for commercial-industrial applications where higher power levels preclude the use of TO-220AB devices. The TO-247AC is similar but superior to the earlier TO-218 package because its isolated mounting hole. It also provides greater creepage distances between pins to meet the requirements of most safety specifications.

| PRODUCT SUMMARY | | |
|---|---|---|
| $V_{DS}$ (V) | 200 | |
| $R_{DS(on)}$ (Ω) | $V_{GS}$ = 10 V | 0.18 |
| $Q_g$ (max.) (nC) | 70 | |
| $Q_{gs}$ (nC) | 13 | |
| $Q_{gd}$ (nC) | 39 | |
| Configuration | Single | |

| ORDERING INFORMATION | |
|---|---|
| Package | TO-247AC |
| Lead (Pb)-free | IRFP240PbF |

**ABSOLUTE MAXIMUM RATINGS** ($T_C$ = 25 °C, unless otherwise noted)

| PARAMETER | | | SYMBOL | LIMIT | UNIT |
|---|---|---|---|---|---|
| Drain-source voltage | | | $V_{DS}$ | 200 | V |
| Gate-source voltage | | | $V_{GS}$ | ± 20 | |
| Continuous drain current | $V_{GS}$ at 10 V | $T_C$ = 25 °C | $I_D$ | 20 | A |
| | | $T_C$ = 100 °C | | 12 | |
| Pulsed drain current [a] | | | $I_{DM}$ | 80 | |
| Linear derating factor | | | | 1.2 | W/°C |
| Single pulse avalanche energy [b] | | | $E_{AS}$ | 510 | mJ |
| Repetitive avalanche current[a] | | | $I_{AR}$ | 20 | A |
| Repetitive avalanche energy[a] | | | $E_{AR}$ | 15 | mJ |
| Maximum power dissipation | $T_C$ = 25 °C | | $P_D$ | 150 | W |
| Peak diode recovery dV/dt [c] | | | dV/dt | 5.0 | V/ns |
| Operating junction and storage temperature range | | | $T_J$, $T_{stg}$ | -55 to +150 | °C |
| Soldering recommendations (peak temperature) [d] | for 10 s | | | 300[d] | |
| Mounting torque | 6-32 or M3 screw | | | 10 | lbf · in |
| | | | | 1.1 | N · m |

**Notes**

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11)
b. $V_{DD}$ = 50 V, starting $T_J$ = 25 °C, L = 1.9 mH, $R_g$ = 25 Ω, $I_{AS}$ = 20 A (see fig. 12)
c. $I_{SD}$ ≤ 18 A, dI/dt ≤ 150 A/μs, $V_{DD}$ ≤ $V_{DS}$, $T_J$ ≤ 150 °C
d. 1.6 mm from case




For technical questions, contact: hvm@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

| THERMAL RESISTANCE RATINGS | | | | |
|---|---|---|---|---|
| **PARAMETER** | **SYMBOL** | **TYP.** | **MAX.** | **UNIT** |
| Maximum junction-to-ambient | $R_{thJA}$ | - | 40 | °C/W |
| Case-to-sink, flat, greased surface | $R_{thCS}$ | 0.24 | - | |
| Maximum junction-to-case (drain) | $R_{thJC}$ | - | 0.83 | |

| **SPECIFICATIONS** ($T_J$ = 25 °C, unless otherwise noted) | | | | | | |
|---|---|---|---|---|---|---|
| **PARAMETER** | **SYMBOL** | **TEST CONDITIONS** | **MIN.** | **TYP.** | **MAX.** | **UNIT** |
| **Static** | | | | | | |
| Drain-source breakdown voltage | $V_{DS}$ | $V_{GS}$ = 0 V, $I_D$ = 250 µA | 200 | - | - | V |
| $V_{DS}$ temperature coefficient | $\Delta V_{DS}/T_J$ | Reference to 25 °C, $I_D$ = 1 mA | - | 0.29 | - | V/°C |
| Gate-source threshold voltage | $V_{GS(th)}$ | $V_{DS}$ = $V_{GS}$, $I_D$ = 250 µA | 2.0 | - | 4.0 | V |
| Gate-source leakage | $I_{GSS}$ | $V_{GS}$ = ± 20 V | - | - | ± 100 | nA |
| Zero gate voltage drain current | $I_{DSS}$ | $V_{DS}$ = 200 V, $V_{GS}$ = 0 V | - | - | 25 | µA |
| | | $V_{DS}$ = 160 V, $V_{GS}$ = 0 V, $T_J$ = 125 °C | - | - | 250 | |
| Drain-source on-state resistance | $R_{DS(on)}$ | $V_{GS}$ = 10 V; $I_D$ = 12 A [b] | - | - | 0.18 | Ω |
| Forward transconductance | $g_{fs}$ | $V_{DS}$ = 50 V, $I_D$ = 12 A [b] | 6.9 | - | - | S |
| **Dynamic** | | | | | | |
| Input capacitance | $C_{iss}$ | $V_{GS}$ = 0 V, $V_{DS}$ = 25 V, f = 1.0 MHz, see fig. 5 | - | 1300 | - | pF |
| Output capacitance | $C_{oss}$ | | - | 400 | - | |
| Reverse transfer capacitance | $C_{rss}$ | | - | 130 | - | |
| Total gate charge | $Q_g$ | $V_{GS}$ = 10 V; $I_D$ = 18 A, $V_{DS}$ = 160 V, see fig. 6 and 13 [b] | - | - | 70 | nC |
| Gate-source charge | $Q_{gs}$ | | - | - | 13 | |
| Gate-drain charge | $Q_{gd}$ | | - | - | 39 | |
| Turn-on delay time | $t_{d(on)}$ | $V_{DD}$ = 100 V, $I_D$ = 18 A, $R_g$ = 9.1 Ω, $R_D$ = 5.4 Ω, see fig. 10 [b] | - | 14 | - | ns |
| Rise time | $t_r$ | | - | 51 | - | |
| Turn-off delay time | $t_{d(off)}$ | | - | 45 | - | |
| Fall time | $t_f$ | | - | 36 | - | |
| Internal drain inductance | $L_D$ | Between lead, 6 mm (0.25") from package and center of die contact  | - | 5.0 | - | nH |
| Internal source inductance | $L_S$ | | - | 13 | - | |
| **Drain-Source Body Diode Characteristics** | | | | | | |
| Continuous source-drain diode current | $I_S$ | MOSFET symbol showing the integral reverse p - n junction diode  | - | - | 20 | A |
| Pulsed diode forward current [a] | $I_{SM}$ | | - | - | 80 | |
| Body diode voltage | $V_{SD}$ | $T_J$ = 25 °C, $I_S$ = 20 A, $V_{GS}$ = 0 V [b] | - | - | 2.0 | V |
| Body diode reverse recovery time | $t_{rr}$ | $T_J$ = 25 °C, $I_F$ = 18 A, dI/dt = 100 A/µs [b] | - | 300 | 610 | ns |
| Body diode reverse recovery charge | $Q_{rr}$ | | - | 3.4 | 7.1 | µC |
| Forward turn-on time | $t_{on}$ | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S$ and $L_D$) | | | | |

**Notes**

a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11)
b. Pulse width ≤ 300 µs; duty cycle ≤ 2 %


For technical questions, contact: hvm@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.

**TYPICAL CHARACTERISTICS** (25 °C, unless otherwise noted)





**Fig. 1 - Typical Output Characteristics, $T_C$ = 25 °C**





**Fig. 2 - Typical Output Characteristics, $T_C$ = 150 °C**





**Fig. 3 - Typical Transfer Characteristics**





**Fig. 4 - Normalized On-Resistance vs. Temperature**





**Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage**





**Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage**



For technical questions, contact: hvm@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.





Fig. 7 - Typical Source-Drain Diode Forward Voltage





Fig. 9 - Maximum Drain Current vs. Case Temperature





Fig. 8 - Maximum Safe Operating Area





Fig. 10a - Switching Time Test Circuit





Fig. 10b - Switching Time Waveforms





Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case



For technical questions, contact: hvm@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.





**Fig. 12a - Unclamped Inductive Test Circuit**





**Fig. 12b - Unclamped Inductive Waveforms**





**Fig. 12c - Maximum Avalanche Energy vs. Drain Current**





**Fig. 13a - Basic Gate Charge Waveform**






**Fig. 13b - Gate Charge Test Circuit**


For technical questions, contact: hvm@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.




**Note**

a. $V_{GS}$ = 5 V for logic level devices


**Fig. 14 - For N-Channel**


*Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91210.*



For technical questions, contact: hvm@vishay.com
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000
Downloaded from Arrow.com.

# TO-247AC (High Voltage)

## VERSION 1: FACILITY CODE = 9






Section C--C,D--D,E--E

| | MILLIMETERS | | | |
|---|---|---|---|---|
| DIM. | MIN. | NOM. | MAX. | NOTES |
| A | 4.83 | 5.02 | 5.21 | |
| A1 | 2.29 | 2.41 | 2.55 | |
| A2 | 1.17 | 1.27 | 1.37 | |
| b | 1.12 | 1.20 | 1.33 | |
| b1 | 1.12 | 1.20 | 1.28 | |
| b2 | 1.91 | 2.00 | 2.39 | 6 |
| b3 | 1.91 | 2.00 | 2.34 | |
| b4 | 2.87 | 3.00 | 3.22 | 6, 8 |
| b5 | 2.87 | 3.00 | 3.18 | |
| c | 0.40 | 0.50 | 0.60 | 6 |
| c1 | 0.40 | 0.50 | 0.56 | |
| D | 20.40 | 20.55 | 20.70 | 4 |

| | MILLIMETERS | | | |
|---|---|---|---|---|
| DIM. | MIN. | NOM. | MAX. | NOTES |
| D1 | 16.46 | 16.76 | 17.06 | 5 |
| D2 | 0.56 | 0.66 | 0.76 | |
| E | 15.50 | 15.70 | 15.87 | 4 |
| E1 | 13.46 | 14.02 | 14.16 | 5 |
| E2 | 4.52 | 4.91 | 5.49 | 3 |
| e | 5.46 BSC | | | |
| L | 14.90 | 15.15 | 15.40 | |
| L1 | 3.96 | 4.06 | 4.16 | 6 |
| Ø P | 3.56 | 3.61 | 3.65 | 7 |
| Ø P1 | 7.19 ref. | | | |
| Q | 5.31 | 5.50 | 5.69 | |
| S | 5.51 BSC | | | |

**Notes**

(1) Package reference: JEDEC® TO247, variation AC
(2) All dimensions are in mm
(3) Slot required, notch may be rounded
(4) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm per side. These dimensions are measured at the outermost extremes of the plastic body
(5) Thermal pad contour optional with dimensions D1 and E1
(6) Lead finish uncontrolled in L1
(7) Ø P to have a maximum draft angle of 1.5° to the top of the part with a maximum hole diameter of 3.91 mm
(8) Dimension b2 and b4 does not include dambar protrusion. Allowable dambar protrusion shall be 0.1 mm total in excess of b2 and b4 dimension at maximum material condition




For technical questions, contact: hvm@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

## VERSION 2: FACILITY CODE = Y




Lead Assignments
1. Gate
2. Drain
3. Source
4. Drain

| | MILLIMETERS | | |
|---|---|---|---|
| DIM. | MIN. | MAX. | NOTES |
| A | 4.58 | 5.31 | |
| A1 | 2.21 | 2.59 | |
| A2 | 1.17 | 2.49 | |
| b | 0.99 | 1.40 | |
| b1 | 0.99 | 1.35 | |
| b2 | 1.53 | 2.39 | |
| b3 | 1.65 | 2.37 | |
| b4 | 2.42 | 3.43 | |
| b5 | 2.59 | 3.38 | |
| c | 0.38 | 0.86 | |
| c1 | 0.38 | 0.76 | |
| D | 19.71 | 20.82 | |
| D1 | 13.08 | - | |

| | MILLIMETERS | | |
|---|---|---|---|
| DIM. | MIN. | MAX. | NOTES |
| D2 | 0.51 | 1.30 | |
| E | 15.29 | 15.87 | |
| E1 | 13.72 | - | |
| e | 5.46 BSC | | |
| Ø k | 0.254 | | |
| L | 14.20 | 16.25 | |
| L1 | 3.71 | 4.29 | |
| Ø P | 3.51 | 3.66 | |
| Ø P1 | - | 7.39 | |
| Q | 5.31 | 5.69 | |
| R | 4.52 | 5.49 | |
| S | 5.51 BSC | | |
| | | | |

**Notes**

(1) Dimensioning and tolerancing per ASME Y14.5M-1994
(2) Contour of slot optional
(3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
(4) Thermal pad contour optional with dimensions D1 and E1
(5) Lead finish uncontrolled in L1
(6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
(7) Outline conforms to JEDEC outline TO-247 with exception of dimension c




For technical questions, contact: hvm@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

## VERSION 3: FACILITY CODE = N




| | MILLIMETERS | |
|---|---|---|
| DIM. | MIN. | MAX. |
| A | 4.65 | 5.31 |
| A1 | 2.21 | 2.59 |
| A2 | 1.17 | 1.37 |
| b | 0.99 | 1.40 |
| b1 | 0.99 | 1.35 |
| b2 | 1.65 | 2.39 |
| b3 | 1.65 | 2.34 |
| b4 | 2.59 | 3.43 |
| b5 | 2.59 | 3.38 |
| c | 0.38 | 0.89 |
| c1 | 0.38 | 0.84 |
| D | 19.71 | 20.70 |
| D1 | 15.97 | - |

| | MILLIMETERS | |
|---|---|---|
| DIM. | MIN. | MAX. |
| D2 | 0.51 | 1.35 |
| E | 15.29 | 15.87 |
| E1 | 13.46 | - |
| e | 5.46 BSC | |
| k | 0.254 | |
| L | 14.20 | 16.10 |
| L1 | 3.71 | 4.29 |
| N | 7.62 BSC | |
| P | 3.56 | 3.66 |
| P1 | - | 7.39 |
| Q | 5.31 | 5.69 |
| R | 4.52 | 5.49 |
| S | 5.51 BSC | |

ECN: E26-0465-Rev. H, 07-Sep-2026
DWG: 5971

**Notes**

(1) Dimensioning and tolerancing per ASME Y14.5M-1994
(2) Contour of slot optional
(3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
(4) Thermal pad contour optional with dimensions D1 and E1
(5) Lead finish uncontrolled in L1
(6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")



For technical questions, contact: hvm@vishay.com

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, “Vishay”), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

*© 2026 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED*



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

Downloaded from Arrow.com.