Part Number : 1200060654
Product Description : Micro-Change (M12) Single-Ended Cordset, 5 Poles, A-Coded, Female (90°) to Pigtail, 0.34mm² Black PVC Cable, 5.0m (16.40') Length
Series Number : 120006
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 805001E03M050



Documents and Resources

Drawings

1200060654_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)6375-DC (05 Nov 2025) SCIP:633f6e45-4f54-4fbf-9af8-b2ca0fe813bb
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120006
Description	Micro-Change (M12) Single-Ended Cordset, 5 Poles, A-Coded, Female (90°) to Pigtail, 0.34mm² Black PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	883906137267

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.80mm (.230")
Cable Length	5.0m (16.40')

Downloaded from Arrow.com.

Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	270.800/g
Orientation	90° to Pigtail
Poles	5
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	22

Downloaded from Arrow.com.