

5

4

3


2

1


Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802

No.1. contact

12,5 max.





screw lock thread



2,9 ±0,3

Printed board layout
component side



Connector retention and insertion forces on the PCB = 25 / 80 Newtons.

09 65 369 3733	M3	1					Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, High temperature, 25 poles, male, straight with solder pins 2.9, screw lock and grounding board lock.	Maßstab/ Scale 1.5:1
09 65 369 6733	M3	2				Detail.	04/09/02	YT			
09 65 369 7733	M3	3				Insp.					
09 65 369 3713	4-40 UNC	1				Stand.					
09 65 369 6713	4-40 UNC	2	31892	22/04/04	JH	 HARTING EURL F-95972 Paris				TB 09 65 369 x7x3	Blatt/ Page 1/
09 65 369 7713	4-40 UNC	3	31084	04/09/02	YT						
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name						