




RCU-G-02.00-AMS-AM

RCU SERIES

IP68 SEALED USB CABLE PLUG

SPECIFICATIONS

For complete specifications
see www.samtec.com?RCU

Insulator Material:

Glass Filled Thermoplastic

Contact Material:

Phosphor Bronze

Current Rating:

4.2 A per pin

(1 pin powered)

Operating Temp Range:

-20 °C to +80 °C

Shield Material:

Phosphor Bronze

Wire:

20 AWG (Power)

25 AWG (Signal)


28 AWG (Drain)

Mates with:
RPCU, RPBU



Solutionator
DESIGN IN A MINUTE

- Easy sealed cable solutions
- Build a standard or flexible custom online
- Calculate performance, current rating, voltage drop
- Live chat with AccliMate™ engineers for custom options
- Variety of shells, pin sizes, signal, power, I/O interfaces
- Assembly and field kits available



DUST CAPS

-AMS = DCA-RCU-01-01-A
-BMS = DCA-RCU-01-01-B

ALSO AVAILABLE (MOQ Required)

- Other wire lengths
- End option 2 with -AMS, -BMS or -BM

RCU

PLATING

-G
= 30 μ" (0.76 μm)
Gold on contact,
Nickel on shell

WIRE LENGTH


-01.00
= (1 m) 40" Cable
-02.00
= (2 m) 79" Cable
Standard lengths

END 1 OPTION

-AMS
= USB A Type,
Sealed
-BMS
= USB B Type,
Sealed

END 2 OPTION

-AM
= USB A Type,
Not Sealed
-BC
= Blunt Cut



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Components must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.