


VGA with Audio over Cat5/Cat6 Transmitter and Receiver with Repeater Kit, Box-Style, 1920x1440 at 60Hz, Up to 1000 ft. TAA

MODEL NUMBER: **B130-111A**



Features

- Kit comes with both local transmitter and remote/repeater units.
- Locate multiple sets of monitors and speakers at different points in a chain of up to 2,000 ft. by connecting additional receiver (B132-100A or B132-100A-WP-1) or repeater (B132-110A) units.
- Up to 4 remote units (3 repeaters and 1 receiver) can be connected together, providing audio/video to up to 4 sets of monitors and speakers
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Extend a 1920 x 1440 (60Hz) video and audio signal up to 500 ft., or a 1024 x 768 (60Hz) video and audio signal up to 1,000 ft., between the local transmitter and the first remote/repeater unit in the installation.
- Extend a 1920 x 1440 (60Hz) video and audio signal up to an additional 500 ft., or a 1024 x 768 (60Hz) video and audio signal up to an additional 1,000 ft., from the first remote/repeater unit to the last set of display and speakers in the installation.
- Features built-in Equalization and Gain controls for video image adjustment.
- Includes mounting hardware that allows wall mounting, rackmounting or pole mounting.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Highlights

- Kit comes with both local transmitter and remote/repeater units
- Locate multiple sets of monitors and speakers at different points in a chain of up to 2,000 ft. by connecting additional receiver (B132-100A or B132-100A-WP-1) or repeater (B132-110A) units
- Up to 4 remote units (3 repeaters and 1 receiver) can be connected together, providing audio/video to up to 4 sets of monitors and speakers
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Computer with VGA video and 3.5mm Audio outputs
- Monitor / TV / Speakers with VGA and 3.5mm Audio inputs

Package Includes

- B130-111A local transmitter unit
- B130-111A remote/repeater unit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- (2) External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; 5V, 2A, 5 ft.)
- Screwdriver for video adjustment
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332161628
Product Type	Cat5/Cat6 Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; 5V, 2A, 5 ft.
Technology	VGA/SVGA; Stereo Audio; Cat5/5e; Cat6
Form Factor and Mounting Options	Box
VIDEO	
Max 720P Range (ft)	500
Max 1080P Range (ft)	500
PHYSICAL	
Color	Black
Number of Displays	1
Shipping Dimensions (hwd / cm)	5.08 x 16.00 x 21.34
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 8.40
Shipping Weight (kg)	0.91
Shipping Weight (lbs.)	2.00
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	1000
Max 480P Range (ft)	1000
Max 1440 x 900 Range (ft)	500
Max 1080i Range (ft)	500
Max 1920 x 1440 Range (ft)	500



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Max 480i Range (ft)	1000
Max 640 x 480 Range (ft)	1000
Max 800 x 600 Range (ft)	1000
Max 1600 x 1200 Range (ft)	500
USB Extension Support	No
CONNECTIONS	
Ports	1
Side A - Connector 1	(2) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Built-In Equalizer	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>