


210 Series

Dividohm® Vitreous Enamel Adjustable Power Resistors



Series	Wattage	Ohms	Dimensions (in. / mm)		Core	Voltage
			Length	Diam.		
D12	12	1.0-10K	1.75 / 44.4	0.313 / 7.94	0.188 / 4.76	565
D25	25	1.0-25K	2.0 / 50.8	0.562 / 14.3	0.313 / 7.94	625
D50	50	1.0-100K	4.0 / 101.6	0.562 / 14.3	0.313 / 7.94	1625
D75	75	1.0-100K	6.0 / 152.4	0.562 / 14.3	0.313 / 7.94	2625
D100	100	1.0-100K	6.5 / 165.1	0.750 / 19.1	0.50 / 12.7	2845
D175	175	1.0-100K	8.5 / 215.9	1.125 / 28.6	0.75 / 19.1	3595
D225	225	1.0-100K	10.5 / 266.7	1.125 / 28.6	0.75 / 19.1	4595
D500	500	1.5-15K	12.0 / 304.8	2.50 / 63.5	1.75 / 44.5	4970
D1000	1000	3.0-27.7K	20.0 / 508.0	2.50 / 63.5	1.75 / 44.5	8900

Other sizes available. Consult factory.
Also available in low cost Centohm coating. Consult Factory.

Power limitations for high resistance values:	Power rating	Resistance value
When resistance exceeds the resistance values listed at right, derate the Power Rating by 25% to improve reliability:	12W	4,500Ω
	25W	9,000Ω
	50W	20,000Ω
	75W	35,000Ω
	100W	50,000Ω
	No power derating necessary for ratings higher than 100 watts.	

Choose Ohmite's 210 Type adjustable resistors for applications requiring settings at different resistance values. These wirewound resistors are equipped with an adjustable lug, making them ideal for adjusting circuits, obtaining odd resistance values and setting equipment to meet various line voltages.

210 Type resistors feature a hollow core to permit secure fastening with spring-type clips or thru bolts with washers. They also offer the durability of lead free vitreous enamel coating and all-welded construction.

Mounting brackets not included with resistors.

FEATURES

- Terminals suitable for soldering or bolt connection.
- Adjustable lug supplied.
- High wattage applications.
- All-welded construction.
- Rugged lead free vitreous enamel coating.
- Flame resistant coating.
- Thumb-screw-adjustable lug available (Part No. 2160) for 1.125" core resistors.

SPECIFICATIONS

Material

Coating: Lead free vitreous enamel.

Core: Tubular ceramic.

Terminals: Solder coated radial lug.

Adjustable terminal: Nickel plated steel. (Screwdriver type adjustable lug supplied standard. Other types, including silver contact units, available.)

Derating: Linearly from 100% @ +25°C to 0% @ +350°C.

Electrical

Tolerance: ±10% (K)

Power rating: Based on 25°C free air rating. The stated wattage rating applies only when the entire resistance is in the circuit. Setting the lug at an intermediate point reduces the wattage rating by the approximate same proportion. Example: If the lug is set at half resistance, the wattage is reduced by approximately one-half.

Overload: 10 times rated wattage for 5 seconds.

Temperature coefficient: ±260 ppm/°C

Dielectric withstanding voltage: 1000 VAC: 12 to 100 watt rating. 3000 VAC: 175 and 225 watt rating (measured from terminal to mounting bracket)

To calculate max. amps: use the formula $\sqrt{P/R}$.

See page 26 for mounting hardware

STOCK PART NUMBERS FOR STANDARD RESISTANCE VALUES

Ohmic value	Part No. Prefix ▶ Suffix ▼	Wattage								Ohmic value	Part No. Prefix ▶ Suffix ▼	Wattage								Ohmic value	Part No. Prefix ▶ Suffix ▼	Wattage							
		12	25	50	75	100	175	225	500			1000	12	25	50	75	100	175	225			500	1000	12	25	50	75	100	175
1.0	—1R0	✓	✚	✚	✓	✚	✚	✚		400	—400	✓	✓	✓	✓		✓	✚	✓	✓	7,500	—7K5	✓	✓	✓	✚			
2	—2R0	✚	✚	✚	✓	✚	✓	✚		500	—500	✚	✓	✚		✚	✓	✚	✓	✓	8,000	—8K0	✚	✚	✚	✚			
3	—3R0	✚	✓		✓		✓	✚		600	—600	✚									8,500	—8K5	✚						
4	—4R0		✓	✓	✚	✚	✚	✓	✚	750	—750	✓	✓	✚	✚						9,000	—9K0	✚	✚	✚	✚			
5	—5R0	✚	✓	✚	✓	✚	✚	✚	✓	800	—800	✚	✓	✓	✚						10,000	—10K	✓	✓	✓	✓	✓	✓	✓
7.5	—7R5	✓	✓							1,000	—1K0	✓	✚	✚		✚	✓	✚	✓	✓	12,000	—12K		✚	✚	✚			
10	—10R	✚	✚	✚	✓	✚	✚	✚		1,250	—1K25	✓	✓	✚	✚						15,000	—15K		✚	✚	✚	✚	✚	
15	—15R	✓	✓		✚					1,500	—1K5	✓	✚	✓	✓		✓	✓			20,000	—20K		✓	✓	✚	✚	✚	
20	—20R	✓	✓							2,000	—2K0	✓	✓	✓	✓		✓	✓			25,000	—25K		✓	✓	✓	✚	✚	
25	—25R	✚	✚	✚	✚	✚	✚	✚		2,250	—2K25	✚	✚	✚	✚						30,000	—30K			✚	✚	✚	✚	
50	—50R	✚	✚	✚	✓	✚	✚	✚		2,500	—2K5	✓	✓	✓	✚	✓	✓	✚			35,000	—35K			✚				
75	—75R	✓	✓	✓	✓					3,000	—3K0	✚	✓	✓	✚						40,000	—40K			✚	✚	✚	✚	
100	—100	✚	✓	✓	✚	✚	✚	✚		3,500	—3K5	✓	✚	✚	✚						45,000	—45K							
150	—150	✓	✓	✚						4,000	—4K0	✓	✚	✚	✚						50,000	—50K		✓	✚	✓	✚		
200	—200	✓	✓	✓	✓					4,500	—4K5	✚	✚	✚	✚						60,000	—60K		✚	✚				
250	—250	✓	✚	✓	✓	✚	✚	✚		5,000	—5K0	✚	✓	✚	✚	✚	✓	✓			75,000	—75K				✚	✚		
300	—300	✓	✓	✚	✚					6,000	—6K0	✓	✓	✓	✚						80,000	—80K			✚				
350	—350	✚								7,000	—7K0	✓	✚	✚	✚						100,000	—100K		✓	✚	✓	✓	✓	

- + = Most popular stock values
 ✓ = Stock values
 + = Non-stock values subject to minimum handling charge per item

Shaded values involve very fine resistance wire and should not be used in critical applications without burn-in and/or thermal cycling.