

MICRO SWITCH

FREEPORT ILLINOIS U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW82128-T

CATALOG LISTING
BZ-2RW82128-T

PAGE 1 OF 1

ISSUE
7

REPLACES

PR-11868

RELEASE NO.

CHECK

CHECK

REVISIONS

A	CO-52975	KAG	JUN 83
B	CO-59351-D	JWB	JUL 91
C	CO-75204B	KDR	FEB 94
D	CO-77585	TSM	MAR 94
E	CO92984	JAS	MAY 98
F	CO93346	DLT	SEP 98

CHECK

CHECK

21 JAN 83

CEB


CHECK

20 JAN 83

CHECK

SLB

FORMTEK




NOTE

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 13 OZ MAX
RELEASE FORCE — — — 4 OZ MIN
DIFFERENTIAL TRAVEL — — .004-.040
OVERTRAVEL — — — .156 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L96 15A-125, 250 OR 480 VAC
1/8 HP-125 VAC; 1/4 HP-250 VAC
1/2 A-125 VDC; 1/4 A-250 VDC

L288
L299
L306



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/04	
ONE PLACE	X,X	0.4/016	X X
TWO PLACES	X,XX	0.15/006	X XX
THREE PLACES	X,XXX		X XXX
ANGLES			

DESIGN UNITS ☐ SI METRIC

US CUSTOMARY ☒

WEIGHT .076 LB