


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	WEIGHT
NMF2 NMF2WH	1.6 LBS/EACH 730 g/EACH

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS:
1- 2RU MANAGER (FRONT ONLY)
1- 2RU 19" COVER
- DIMENSIONS IN PARENTHESIS ARE METRIC.

MAX STORAGE TEMPERATURE 65°C (149°F)
MAX OPERATING TEMPERATURE 60°C (140°F)



A

A

TITLE				
NMF2 CABLE MANAGER				
CUSTOMER DRAWING				
ITEM REVISION NAME			V10404AF/02	
DATASET FILE NAME			V10404AF_DC/02B	
		THIRD ANGLE PROJECTION		
MATERIAL			DRAWING NUMBER	
MANAGER: ABS 2RU COVER: PVC			10404-16	
DRAWN BY	DATE	CHK	SCALE	SIZE
BAME	3/6/07	TCK	NONE	A
SHEET 1 OF 1				

02B	4/29/20	JBO	JCO	JEFK	ADDED TEMPERATURE NOTE	M09000LT
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

2

1