


Thick Film Surface Mount Chip Resistors, Wraparound, Extremely Low Value (0.01 Ω to 0.976 Ω)



DESIGN SUPPORT TOOLS

[click logo to get started](#)

3D
Models
Available

FEATURES

- Extremely low resistance values (0.01 Ω to 0.976 Ω)
- Sulfur resistant (per ASTM B809-95 humid vapor test)
- Enhanced power rating due to long side terminal construction (0612, 1020 types)
- Suitable for current sensing and shunts
- Metal glaze on high quality ceramic
- Protective overglaze
- Lead (Pb)-free solder contacts on Ni barrier layer
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

STANDARD ELECTRICAL SPECIFICATIONS

GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70^{\circ}\text{C}}$ W	TEMPERATURE COEFFICIENT \pm ppm/ $^{\circ}\text{C}$	RESISTANCE RANGE Ω	TOLERANCE \pm %	E-SERIES ⁽²⁾
RCWE0402	0402	0.125	400	0.033 to 0.05	5.0	24
			200	0.051 to 0.196	1.0, 5.0	24; 96
			100	0.2 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE0603	0603	0.2	700	0.010 to 0.018	5.0	24
			400	0.02 to 0.0324	1.0, 5.0	24; 96
			200	0.033 to 0.105	1.0, 5.0	
			100	0.11 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE0805	0805	0.25	400	0.010 to 0.018	5.0	24
			300	0.02 to 0.0324	1.0, 5.0	24; 96
			200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE0612	0612	1.0	300	0.010 to 0.016	2.0, 5.0	24
			200	0.018 to 0.2	2.0, 5.0	24; 96
			100	0.205 to 0.976	1.0, 5.0	
RCWE1206	1206	0.5	600	0.010 to 0.018	5.0	24
			300	0.02 to 0.0324	1.0, 5.0	24; 96
			200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE1210	1210	1.0	500	0.010 to 0.018	5.0	24
			300	0.02 to 0.0324	1.0, 5.0	24; 96
			200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE1020	1020	2.0	200	0.010 to 0.016	2.0, 5.0	24
			100	0.0162 to 0.976	1.0, 5.0	24; 96
RCWE2010	2010	1.0	600	0.010 to 0.018	5.0	24
			300	0.02 to 0.0324	1.0, 5.0	24; 96
			200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	
RCWE2512	2512	2.0	600	0.010 to 0.018	5.0	24
			300	0.02 to 0.0324	1.0, 5.0	24; 96
			200	0.033 to 0.05	1.0, 5.0	
			100	0.051 to 0.976	0.5 ⁽¹⁾ , 1.0, 5.0	

GLOBAL PART NUMBER INFORMATION

Global Part Numbering example: RCWE060351L0FNEA (visit www.vishay.net Vishay Dale parts numbering manual for all options)

R **C** **W** **E** **0** **6** **0** **3** **5** **1** **L** **0** **F** **N** **E** **A**

GLOBAL MODEL (8 digits)

RCWE0402
RCWE0603
RCWE0805
RCWE0612
RCWE1206
RCWE1210
RCWE1020
RCWE2010
RCWE2512

VALUE (4 digits)

L = mΩ *
R = decimal
10L0 = 0.01 Ω
R470 = 0.47 Ω

Note:

* Use "L" for resistance values < 0.1 Ω

TOLERANCE (1 digit)

D = ± 0.5 %
F = ± 1.0 %
G = ± 2.0 %
J = ± 5.0 %

TCR (1 digit)

K = ± 100 ppm/°C
N = ± 200 ppm/°C
M = ± 300 ppm/°C
Q = ± 400 ppm/°C
P = ± 500 ppm/°C
T = ± 600 ppm/°C
G = ± 700 ppm/°C

PACKAGING (2 digits)

EA = lead (Pb)-free, tape/reel

SPECIAL (up to 2 digits)


(dash number) from **1** to **99** as applicable

TECHNICAL SPECIFICATIONS


PARAMETER	UNIT	0402	0603	0805	0612	1206	1210	1020	2010	2512
Operating temperature range	°C	-55 to +155								
Maximum operating voltage	V	(P × R) ^{1/2}								
Insulation voltage U_{ins} (1 min)	V	> 75	> 100	> 200	> 100	> 300	> 300	> 300	> 300	> 300
Insulation resistance	Ω	> 10 ⁹								
Weight/1000 pieces (typical)	g	0.7	3	5.5	11.5	10.5	17.5	27.5	26	40.5

DIMENSIONS

RCWE0402 to RCWE2512



RCWE0612, RCWE1020




- 3D models available: www.vishay.com/doc?31106
- Surface mount solder profile recommendations: www.vishay.com/doc?31052

SIZE	DIMENSIONS in millimeters						SOLDER PAD DIMENSIONS in millimeters		
	RESISTANCE RANGE Ω	L	W	H	T1	T2	a	b	l
0402	0.033 to 0.976	1.05 ± 0.05	0.55 ± 0.05	0.35 ± 0.1	0.3 ± 0.15	0.25 ± 0.1	0.7	0.7	0.3
0603	0.01 to 0.03	1.6 ± 0.1	0.85 ± 0.1	0.5 ± 0.1	0.5 ± 0.2	0.3 ± 0.2	0.9	1.0	0.4
	0.033 to 0.976				0.3 ± 0.2		0.7	1.0	0.8
0805	0.01 to 0.03	2.0 ± 0.15	1.3 ± 0.1	0.55 ± 0.1	0.6 ± 0.2	0.35 ± 0.2	1.0	1.4	0.6
	0.033 to 0.976				0.4 ± 0.2		0.8	1.4	1.0
0612	0.01 to 0.976	1.6 ± 0.2	3.2 ± 0.2	0.6 ± 0.1	0.4 ± 0.15	0.25 ± 0.15	0.9	3.5	0.8
1206	0.01 to 0.03	3.1 ± 0.15	1.6 ± 0.15	0.6 ± 0.1	0.9 ± 0.2	0.45 ± 0.2	1.3	1.8	1.0
	0.033 to 0.05				0.8 ± 0.2		1.2	1.8	1.2
	0.051 to 0.976				0.45 ± 0.2		1.0	1.8	1.6
1210	0.01 to 0.03	3.1 ± 0.2	2.5 ± 0.2	0.6 ± 0.1	0.8 ± 0.2	0.4 ± 0.2	1.3	2.6	1.1
	0.033 to 0.976				0.4 ± 0.2		0.9	2.6	2.0
1020	0.01 to 0.976	2.5 ± 0.2	5.0 ± 0.2	0.6 ± 0.1	0.55 ± 0.15	0.30 ± 0.15	1.2	5.5	1.4
2010	0.01 to 0.03	5.0 ± 0.2	2.5 ± 0.15	0.6 ± 0.1	1.6 ± 0.3	0.6 ± 0.2	2.3	3.0	1.4
	0.033 to 0.05				0.7 ± 0.3		1.4	3.0	3.2
	0.051 to 0.976				0.7 ± 0.3		1.4	3.0	3.2

DIMENSIONS

RCWE0402 to RCWE2512


RCWE0612, RCWE1020




- 3D models available: www.vishay.com/doc?31106
- Surface mount solder profile recommendations: www.vishay.com/doc?31052


SIZE	DIMENSIONS in millimeters						SOLDER PAD DIMENSIONS in millimeters		
	RESISTANCE RANGE Ω	L	W	H	T1	T2	a	b	l
2512	0.01 to 0.03	6.3 \pm 0.2	3.15 \pm 0.15	0.6 \pm 0.1	2.0 \pm 0.3	0.6 \pm 0.2	2.8	3.6	1.4
	0.033 to 0.05				0.8 \pm 0.3		1.6		3.8
	0.051 to 0.976				0.8 \pm 0.3		1.6		3.8

DERATING



SINGLE PULSE



SINGLE PULSE


PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Thermal shock	MIL-STD-202, method 107, -55 °C to +125 °C, 300 cycles at each extreme	± 1.0 % + 0.0005 Ω
Short time overload	2x rated power; size and duration - 0402: 0.5 s, 0603 and 0805: 1 s, 1206 and larger: 2 s	± 0.5 % + 0.0005 Ω
High temperature exposure	MIL-STD-202, method 108, 1000 h at T = 125 °C, 0 % power	± 2.0 % + 0.0005 Ω
Temperature cycling	JESD 22, method JA-104, 1000 cycles (-55 °C to +125 °C)	± 2.0 % + 0.0005 Ω
Biased humidity	MIL-STD-202, method 103, 1000 h 85 °C/85 % RH, 10 % x (P x R) ^{1/2}	± 2.0 % + 0.0005 Ω
Mechanical shock	MIL-STD-202, method 213, condition C, 10 g's, 6 ms (half sine), 3 directions	± 1.0 % + 0.0005 Ω
Vibration	MIL-STD-202, method 204, 5 g's, 20 min, 12 cycles, 3 directions, 10 Hz to 2000 Hz	± 1.0 % + 0.0005 Ω
Operational life	MIL-STD-202, method 108, 1000 h at T = 125 °C at rated power	± 2.0 % + 0.0005 Ω
Resistance to solder heat	MIL-STD-202, method 210, +260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 1.0 % + 0.0005 Ω
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	± 2.0 % + 0.0005 Ω

PACKAGING					
MODEL	REEL				
	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	CODE
RCWE0402	8 mm/punched paper	180 mm/7"	2 mm	10 000	EA
RCWE0603	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE0805	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE0612	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE1206	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE1210	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE1020	12 mm/embossed plastic	180 mm/7"	4 mm	4000	EA
RCWE2010	12 mm/embossed plastic	180 mm/7"	4 mm	4000	EA
RCWE2512	12 mm/embossed plastic	180 mm/7"	8 mm	2000	EA

Notes

- Embossed carrier tape per EIA-481-1A
- Additional packaging details at: www.vishay.com/doc?31543



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.