

Johanson Part Number 2450FB15L0001001E

Johanson Part Number:	2450FB15L0001001E	Johanson Company:	JTI
Legacy P/N:	2450FB15L0001E	Size for Capacitors (EIA):	None
Description:	RF Bal Filt, 0805, 2400-2500MHz, 2W, 1.5dB, Ag/Pt (RoHS), Harmonic Filter-Balun for AT86RF230/231 & ATmega128RFA1, 7" Reel Embossed Tape	Specification Number:	None
Life Cycle Stage:	Active - Production	NCNR:	No
AEC Q200 Qualified:	No	Thickness (Max):	0.035
Schedule B:	8534	Thickness (Min):	0.027
ITAR:	No	End Band(Min):	0.01
ECCN:	EAR99	End Band (max):	0.016
RoHS Compliance:	Yes, RoHS 10/10	Standard Item:	Yes
REACH:	Yes	Lead Time Typical (Weeks)*:	
Country of Origin:	TW	*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.	14
Product Family:	Integrated Passive Components	Length (Min):	0.075
Product Subfamily:	RF Balun Filters	Length (Max):	0.083
Capacitance Value:	None	Width (Min):	0.045
Cap Unit of Meas:	None	Width (Max):	0.053
Tolerance:	None	Packaging:	7" Reel Embossed Tape
Voltage:	None	Packaging Qty:	4000
Dielectric Temp Coefficient:	None	Operating Temp Range:	-40°C to +125°C
Termination:	0	Storage Temp Range (Packaged):	-65°C to +125°C
Marking:	Special	Storage Temp Range (None Operating):	+5°C to +40°C with RH 20% to 70%
Product Release Date:	May 20, 2009, 7 a.m.	Download this information page	Download
Web Page Link:	https://johansontechnology.com/chipset-specific		

Quick Links

- [Home](#)
- [About](#)
- [Contact](#)
- [News](#)
- [Events](#)
- [Do Not Sell My Personal Information](#)

Certifications



Visit Our Affiliate Site



[Johanson Technology](#) is dedicated to providing the highest level of customer satisfaction through high quality components, superior customer service and forward looking, advanced products.

© All rights reserved. [Johanson Technology](#)