ABC275 Series

Ultra-Low Profile Open Frame Power Supplies

Not For New Design
Please refer to exact equivalent product series
ULP275

NOT FOR NEW DESIGN



The ABC275 Series of ultra low profile open frame power supplies feature a wide universal AC input range of 80 – 264 VAC, offering output power 275 W with 13 CFM forced air cooling, or up to 160 W with convection cooling. The power supplies are available in a variety of isolated single output voltages.

The high efficiency and high power density of the ABC family ensures minimal power loss in end-use equipment, thereby facilitating higher reliability, easier thermal management and meets regulatory approvals for environmentally-friendly end products.

These power supplies are ideal for broad range of telecom, datacom, industrial equipment and other applications.

RoHS Compliant

Key Features & Benefits

- 5 x 3 x 0.75 Inch Form Factor
- 275 Watts with Forced Air Cooling
- Efficiencies up to 92%
- -40 to 70°C Operating Temperature
- IEC / EN / UL 62368-1 Compliant
- 12 V / 0.5 A Fan Output
- Thermal Shut-Down Feature
- 3.37 million Hours, Telcordia -SR332-issue 3 MTBF
- No Load Power < 0.5 W

Applications

- Instrumentation
- Lighting
- Industrial Applications
- Applied Computing
- Renewable Energy
- Test and Measurement
- Robotics
- Wireless Communication

bel POWER SOLUTIONS & PROTECTION
a bel group

belfuse.com/power-solutions

Please read our datasheet & drawing disclaimer here.

Downloaded from Arrow.com.

1. MODEL SELECTION

MODEL NUMBER [1]	OUTPUT CONNECTOR	VOLTAGE	MAX. LOAD			POWER
			CONVECTION 50°C (152 W)	CONVECTION 40°C (160 W)	13 CFM (275 W)	
ABC275-1T12L ABC275-1012L	Screw Terminal Header Molex Connector	12 V	12.5 A	13.33 A	22.92 A	275 W
ABC275-1T15L ABC275-1015L	Screw Terminal Header Molex Connector	15 V	10 A	10.66 A	18.33 A	275 W
ABC275-1T24L ABC275-1024L	Screw Terminal Header Molex Connector	24 V	6.25 A	6.67 A	11.46 A	275 W
ABC275-1T30L ABC275-1030L	Screw Terminal Header Molex Connector	30 V	5 A	5.33 A	9.17 A	275 W
ABC275-1T48L ABC275-1048L	Screw Terminal Header Molex Connector	48 V	3.12 A	3.33 A	5.73 A	275 W
ABC275-1T58L ABC275-1058L	Screw Terminal Header Molex Connector	58 V	2.58 A	2.76 A	4.74 A	275 W
COVER-275-XBC [2]	Metal Cover Kit (accessory)					

[1] Class II version available. Add suffix "-2" at the end of the Model Number. Class II means without input Earth pin.
[2] When used in Cover Kit, de-rate output power to 70 % under all operating conditions.

2. INPUT SPECIFICATIONS

Specifications are for nominal input voltage, 25°C unless otherwise stated.

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Input Voltage	Universal (Derate from 100% at 100 VAC to 72% for forced cooling and 69% for convection cooling at 80 VAC)	80 – 264 VAC / 390 VDC
Input Frequency		47-63 Hz
Input Current	115 VAC: 230 VAC:	2.6 A max. 1.3 A max.
No Load Power	Typical	< 0.5 W
Inrush Current	115 VAC: 230 VAC: 264 VAC:	25 A 45 A 75 A
Leakage Current	Typical (N/A for Class II Option) Touch current	300 µA < 100 µA
Switching Frequency	PFC PWM	70 – 130 kHz 50 – 80 kHz

NOT FOR NEW DESIGN

Downloaded from Arrow.com.

3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Output Voltage	Refer to Model selection table	From 12 V to 58 V
Output Power [3]	13 CFM (forced air cooling) Convection (natural cooling)	275 W up to 160 W
Efficiency	48 V, 58 V: 24 V, 30 V: 12 V, 15 V:	92% 90% 88%
Hold-up Time	At 275 W: At 160 W:	8 ms 16 ms
Power Factor	@ Full Load	> 0.95
Line Regulation [4]		± 0.5%
Load Regulation [4]		± 1%
Minimum Load		0.0 A
Transient Response	25% step load change, at 0.1 A/ µs slew rate, 50% duty cycle, 50 Hz = 4%	recovery time < 5 ms
Ripple [4, 5]	24, 30, 48 & 58 V outputs 12 V & 15 V outputs	1.0 % max. 2.0 % max.
Output Voltage Adjustment [6]		± 3%
Rise Time	Typical	55 ms
Set Point Tolerance [4]		± 1%
Over Current Protection		> 110%
Over Voltage Protection		110 to 140%
Short Circuit Protection	Hiccup mode	
Cooling	With 13 CFM forced air cooling (100 to 264 VAC) [7] With natural convection cooling (100 to 264 VAC) [8]	275 W Up to 160 W

[3] Combined output power of main output, fan supply shall not exceed max. power rating.
[4] Fan supply output voltage tolerance including set point accuracy, line and load regulation is ± 10% and ripple and noise is less than 10%.
[5] Ripple is peak to peak with 20 MHz bandwidth and 10 µF (Electrolytic capacitor) in parallel with a 0.1 µF capacitor at rated line voltage and load ranges.
[6] Adjustment potentiometer is located on the SMT side of the PCB
[7] Refer to Mechanical Drawing
[8] Refer to Derating Curve

4. EMC SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Conducted Emissions	EN 55032-B, CISPR22-B, FCC PART15-B	Pass
Radiated Emissions	EN 55032 A with external core (King core K5B RC 25x12x15-M in input cable)	Pass Level B
Input Current Harmonics	EN 61000-3-2	Class D
Voltage Fluctuation and Flicker	EN 61000-3-3	Pass
ESD Immunity	EN 61000-4-2	Level 3, Criterion A
Radiated Field Immunity	EN 61000-4-3	Level 3, Criterion A
Electrical Fast Transient Immunity	EN 61000-4-4	Level 3, Criterion A
Surge Immunity	EN 61000-4-5	Level 3, Criterion A
Conducted Immunity	EN 61000-4-6	Level 3, Criterion A
Magnetic Field Immunity	EN 61000-4-8	Level 3, Criterion A
Voltage Dips, Interruptions	EN 61000-4-11	Criterion A & B

NOT FOR NEW DESIGN

© 2022 Bel Power Solutions & Protection

Downloaded from Arrow.com.

5. SAFETY SPECIFICATIONS


PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Isolation Voltage	Input to Output: (for ITE applications) Input to GND: (N/A for Class II Option)	4000 VDC 2500 VDC
Safety Standard(s)	EN / IEC / UL 62368-1(Ed .3)	
Agency Approvals	Nemko, UL, C-UL	
CE mark	Complies with LVD Directive	

6. ENVIRONMENTAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION	SPECIFICATION
Operating Temperature [9]	-40 to 0°C startup guaranteed, with spec deviation	-40 to +70°C
Storage Temperature		-40 to +85°C
Relative Humidity	Non-condensing	5% to 95%
Altitude	Operating: Non-operating:	16,000 ft. 40,000 ft.
MTBF	Telcordia -SR332-issue 3	3.37 million hours

[9] Output ripple can be more than 10% of the output voltage.

DERATING CURVES



Convection load: 160 W up to 40 °C
De-rate between 40-50 °C @ 0.625% per °C
De-rate above 50 °C @ 2.33% per °C

Forced air cooled load: 275 W up to 50°C
De-rate above 50 °C @ 2.5% per °C

Figure1. Derating Curves

Downloaded from Arrow.com.

7. CONNECTOR & PIN DESCRIPTION

CONNECTOR	PIN	DESCRIPTION / CONDITION	MANUFACTURER / PN
AC Input Connector	J1	Pin 1 AC Line Pin 2 Not Fitted Pin 3 AC Neutral	Molex: 26-60-4030 Mating: 09-50-3031; Pins: 08-50-0106
DC Output Connector	J2	Pin 1, 2, 3 V1 +VE Pin 4. 5. 6 V1 -VE	Option 1 (Screw Terminal): Molex: 39357 Series or equivalent Option 2 (Molex Connector): Molex: 26-60-4060 Mating: 09-50-3061; Pins: 08-50-0106
Aux (Fan) Output	J3	Pin 1 FAN +VE Pin 2 FAN -VE	AMP: 640456-2 Mating: 640440-2

8. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITION
Weight	approx. 200 g
Dimensions	127 x 76.2 x 19.05 mm (5 x 3 x 0.75 inches)




Figure 2. Mechanical Drawing – Option 1 (Output Connector – Screw Terminal)

NOTES: In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

1 Stand off, used to mount PCB has OD of 5.4 mm max.
2 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
3 Washer, if used, to have dia of 6.5 mm max.

NOT FOR NEW DESIGN

© 2022 Bel Power Solutions & Protection

Downloaded from Arrow.com.




Figure 3. Mechanical Drawing – Option 2 (Output Connector – Header Molex)

NOTES: In case the PCB is mounted in a metal enclosure, using metal hardware ensure the following:

4 Stand off, used to mount PCB has OD of 5.4 mm max.
5 Screws, used to fix PCB on stand off, have head dia of 6.0 mm max.
6 Washer, if used, to have dia of 6.5 mm max.

NOT FOR NEW DESIGN

Downloaded from Arrow.com.




Figure 4. Mechanical Drawing – Cover Kit Option

NOT FOR NEW DESIGN

For more information on these products consult: tech.support@psbel.com

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.
TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.

bel POWER SOLUTIONS & PROTECTION
a bel group

Asia-Pacific +86 755 298 85888
Europe, Middle East +353 61 49 8941
North America +1 866 513 2839

© 2022 Bel Power Solutions & Protection

Downloaded from Arrow.com.