


REVISIONS																			
LTR	DESCRIPTION												DATE (YR-MO-DA)				APPROVED		
A	Change to military format. Remove approved vendor CAGE 31757.												88-11-08				W. Heckman		
B	Reinstate vendor CAGE 31757. Document updated with editorial changes throughout. Changed to reflect MIL-H-38534 processing.												90-01-10				W. Heckman		
C	Document updated with editorial changes throughout. Changed to reflect current MIL-H-38534 processing.												90-08-09				W. Heckman		
D	Added case outlines X and Y. Editorial changes throughout												93-08-31				K. A. Cottongim		
E	Changes in accordance with NOR 5962-R032-94.												93-11-12				K. A. Cottongim		
F	Added case outline Z. Rewrite entire document.												94-04-07				K. A. Cottongim		
G	Changes in accordance with NOR 5962-R001-96.												95-10-10				K. A. Cottongim		
H	Correct generic number added in NOR 5962-R001-96. Update document to current MIL-PRF-38534 requirements.												00-10-13				Raymond Monnin		
J	Correct Descriptive designator for case outline F. Change CDFP4-P16 to CDFP4-F16. Also update drawing to current boiler plate. gjc												02-07-01				Raymond Monnin		
K	Update drawing.												06-12-07				Raymond Monnin		
<p>THE ORIGINAL FIRST PAGE OF THIS DRAWING HAS BEEN REPLACED.</p> <p>CURRENT CAGE CODE 67268</p>																			
REV																			
SHEET																			
REV																			
SHEET																			
REV STATUS				REV		K	K	K	K	K	K	K	K	K	K	K	K		
OF SHEETS				SHEET		1	2	3	4	5	6	7	8	9	10	11	12		
PMIC N/A				PREPARED BY Gary Zahn					DEFENSE SUPPLY CENTER COLUMBUS P O BOX 3990 COLUMBUS, OHIO 43218-3990 http://www.dscc.dla.mil										
STANDARD MICROCIRCUIT DRAWING THIS DRAWING IS AVAILABLE FOR USE BY ALL DEPARTMENTS AND AGENCIES OF THE DEPARTMENT OF DEFENSE AMSC N/A				CHECKED BY Robert M. Heber															
				APPROVED BY William K. Heckman															
				DRAWING APPROVAL DATE 84-08-10															
				REVISION LEVEL K					SIZE A	CAGE CODE 14933		83024							
									SHEET		1 OF 12								

1. SCOPE

1.1 Scope. This drawing documents one product assurance class, class H (high reliability) and a choice of case outlines and lead finishes are available and are reflected in the Part or Identifying Number (PIN).

1.2 PIN. The PIN shall be as shown in the following example:



1.2.1 Device type(s). The device type(s) identify the circuit function as follows:

<u>Device type</u>	<u>Generic number</u>	<u>Circuit function</u>
01	6N140A, HCPL-6751	4-channel optical coupler

1.2.2 Case outline(s). The case outline(s) are as designated in MIL-STD-1835 and as follows:

<u>Outline letter</u>	<u>Descriptive designator</u>	<u>Terminals</u>	<u>Package style</u>
E	CDIP2-T16	16	Dual-in-line
F	CDFP4-F16	16	Flat pack
X	See figure 1	16	Dual-in-line
Y	See figure 1	16	Dual-in-line
Z	See figure 1	16	Dual-in-line

1.2.3 Lead finish. The lead finish shall be as specified in MIL-PRF-38534.

1.3 Absolute maximum ratings. 1/

Supply voltage (V_{CC})	-0.5 V dc to +20 V dc <u>2/</u>
Peak input current (each channel, ≤ 1 ms duration)	20 mA
Average input current, I_F (each channel).....	10 mA <u>3/</u>
Reverse input voltage, V_R (each channel).....	5 V dc
Output current, I_O (each channel)	40 mA
Output voltage, V_O (each channel).....	-0.5 V dc to +20 V dc <u>2/</u>
Output power dissipation (each channel)	50 mW <u>4/</u>
Storage temperature	-65°C to +150°C
Junction temperature (T_J)	+175°C
Lead solder temperature (soldering, 10 seconds).....	+260°C (1.6 mm below seating plane)
Thermal resistance, junction-to-case (θ_{JC}):	
Case outlines E and F	See MIL-STD-1835
Case outlines X, Y, and Z.....	28°C/W
Case temperature (T_C).....	+170°C

- 1/ Stresses above the absolute maximum rating may cause permanent damage to the device. Extended operation at the maximum levels may degrade performance and affect reliability.
- 2/ Pin 10 should be the most negative voltage at the detector side.
Keeping V_{CC} as low as possible, but greater than 2.0 volts, will provide the lowest total I_{OH} over temperature.
- 3/ Derate I_F at 0.33 mA/°C above +110°C.
- 4/ Output power is collector output power plus one fourth of total supply power. Derate at 1.66 mW/°C above +110°C.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 2

1.4 Recommended operating conditions.

Supply voltage range	2.0 V dc minimum to 18 V dc maximum
High level input current	0.5 mA dc minimum (each channel) up to 5 mA dc maximum
Low level input voltage.....	0.8 V maximum (each channel)
Ambient operating temperature range (T _A)	-55°C to +125°C

2. APPLICABLE DOCUMENTS

2.1 Government specification, standards, and handbooks. The following specification, standards, and handbooks form a part of this drawing to the extent specified herein. Unless otherwise specified, the issues of these documents are those cited in the solicitation or contract.

DEPARTMENT OF DEFENSE SPECIFICATION

MIL-PRF-38534 - Hybrid Microcircuits, General Specification for.

DEPARTMENT OF DEFENSE STANDARDS

MIL-STD-883 - Test Method Standard Microcircuits.
MIL-STD-1835 - Interface Standard for Electronic Component Case Outlines.

DEPARTMENT OF DEFENSE HANDBOOKS

MIL-HDBK-103 - List of Standard Microcircuit Drawings.
MIL-HDBK-780 - Standard Microcircuit Drawings.

(Copies of these documents are available online at <http://assist.daps.dla.mil/quicksearch/> or <http://assist.daps.dla.mil> or from the Standardization Document Order Desk, 700 Robbins Avenue, Building 4D, Philadelphia, PA 19111-5094.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing takes precedence. Nothing in this document, however, supersedes applicable laws and regulations unless a specific exemption has been obtained.

3. REQUIREMENTS

3.1 Item requirements. The individual item performance requirements for device class H shall be in accordance with MIL-PRF-38534. Compliance with MIL-PRF-38534 may include the performance of all tests herein or as designated in the device manufacturer's Quality Management (QM) plan or as designated for applicable device class. The manufacturer may eliminate, modify or optimize the tests and inspections herein, however the performance requirements as defined in MIL-PRF-38534 shall be met for the applicable device class. In addition, the modification in the QM plan shall not affect the form, fit, or function of the device for the applicable device class.

3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-PRF-38534 and herein.

3.2.1 Case outline(s). The case outline(s) shall be in accordance with 1.2.4 herein and figure 1.

3.2.2 Terminal connections. The terminal connections shall be as specified on figure 2.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 3

3.3 Electrical performance characteristics. Unless otherwise specified herein, the electrical performance characteristics are as specified in table I and shall apply over the full specified operating temperature range.

3.4 Electrical test requirements. The electrical test requirements shall be the subgroups specified in table II. The electrical tests for each subgroup are defined in table I.

3.5 Marking of device(s). Marking of device(s) shall be in accordance with MIL-PRF-38534. The device shall be marked with the PIN listed in 1.2 herein. In addition, the manufacturer's vendor similar PIN may also be marked.

3.6 Data. In addition to the general performance requirements of MIL-PRF-38534, the manufacturer of the device described herein shall maintain the electrical test data (variables format) from the initial quality conformance inspection group A lot sample, for each device type listed herein. Also, the data should include a summary of all parameters manually tested, and for those which, if any, are guaranteed. This data shall be maintained under document revision level control by the manufacturer and be made available to the preparing activity (DSCC-VA) upon request.

3.7 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to supply to this drawing. The certificate of compliance (original copy) submitted to DSCC-VA shall affirm that the manufacturer's product meets the performance requirements of MIL-PRF-38534 and herein.

3.8 Certificate of conformance. A certificate of conformance as required in MIL-PRF-38534 shall be provided with each lot of microcircuits delivered to this drawing.

4. VERIFICATION

4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with MIL-PRF-38534 or as modified in the device manufacturer's Quality Management (QM) plan. The modification in the QM plan shall not affect the form, fit, or function as described herein.

4.2 Screening. Screening shall be in accordance with MIL-PRF-38534. The following additional criteria shall apply:

a. Burn-in test, method 1015 of MIL-STD-883.

(1) Test condition A, B, C, or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to either DSCC-VA or the acquiring activity upon request. Also, the test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1015 of MIL-STD-883.

(2) T_A as specified in accordance with table I of method 1015 of MIL-STD-883.

b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 4

TABLE I. Electrical performance characteristics.

Test	Symbol	Conditions -55°C ≤ T _C ≤ +125°C unless otherwise specified	Group A subgroups	Device type	Limits		Unit
					Min	Max	
Low level output voltage	V _{OL}	V _{CC} = 4.5 V, I _F = 0.5 mA, I _{OL} = 1.5 mA <u>1/</u>	1,2,3	01		0.4	V
		V _{CC} = 4.5 V, I _F = 5 mA, I _{OL} = 10 mA <u>1/</u>				0.4	
Current transfer ratio	h _{F(CTR)}	V _O = 0.4 V, I _F = 0.5 mA, V _{CC} = 4.5 V <u>1/ 2/</u>	1,2,3	01	300		%
		V _O = 0.4 V, I _F = 1.6 mA, V _{CC} = 4.5 V <u>1/ 2/</u>			300		
		V _O = 0.4 V, I _F = 5 mA, V _{CC} = 4.5 V <u>1/ 2/</u>			200		
High level output current	I _{OH}	V _{CC} = 18 V, V _O = 18 V, I _F = 2 μA <u>1/ 3/</u>	1,2,3	01		250	μA dc
High level supply current	I _{CCH}	V _{CC} = 18 V, I _{F1} = I _{F2} = I _{F3} = I _{F4} = 0 mA	1,2,3	01		40	μA dc
Low level supply current	I _{CCL}	V _{CC} = 18 V, I _{F1} = I _{F2} = I _{F3} = I _{F4} = 1.6 mA	1,2,3	01		4	mA dc
Input forward voltage	V _F	I _F = 1.6 mA <u>1/</u>	1,2	01		1.7	V dc
			3			1.8	
Input reverse breakdown voltage	V _{BR}	I _R = 10 μA <u>1/</u>	1,2,3	01	5.0		V dc
Input to output insulation leakage current	I _{IO}	V _{IO} = 1500 V dc, <u>4/</u> Relative humidity = 45%, t = 5 seconds, T _A = +25°C	1	01		1.0	μA dc

See footnotes at end of table.

**STANDARD
MICROCIRCUIT DRAWING**

DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43218-3990

SIZE
A

REVISION LEVEL
K

83024

SHEET
5

TABLE I. Electrical performance characteristics - Continued.

Test	Symbol	Conditions -55°C ≤ T _C ≤ +125°C unless otherwise specified	Group A subgroups	Device type	Limits		Unit
					Min	Max	
Capacitance between input-output	C _{IO}	f = 1 MHz, T _A = +25°C, <u>1/</u> <u>5/</u> <u>6/</u>	4	01		4	pF
Propagation delay time, low to high output level	t _{PLH}	I _F = 0.5 mA, R _L = 4.7 kΩ, V _{CC} = 5.0 V <u>1/</u>	9,10,11	01		60	μs
		I _F = 5 mA, R _L = 680Ω, V _{CC} = 5.0 V <u>1/</u>	9	01		20	μs
			10,11			30	
Propagation delay time, high to low output level	t _{PHL}	I _F = 0.5 mA, R _L = 4.7 kΩ, V _{CC} = 5.0 V <u>1/</u>	9,10,11	01		100	μs
		I _F = 5 mA, R _L = 680Ω, V _{CC} = 5.0 V <u>1/</u>	9	01		5	μs
			10,11			10	
Common mode transient immunity at high output level	CM _H	V _{CM} = 25 V (peak), V _{CC} = 5.0 V, R _L = 1.5 kΩ, I _F = 0 mA, <u>1/</u> <u>6/</u> <u>7/</u> <u>8/</u>	9,10,11	01	500		V/μs
Common mode transient immunity at low output level	CM _L	V _{CM} = 25 V (peak), V _{CC} = 5.0 V, R _L = 1.5 kΩ, I _F = 1.6 mA, <u>1/</u> <u>6/</u> <u>8/</u> <u>9/</u>	9,10,11	01	500		V/μs

1/ Each channel.2/ Current transfer ratio is defined as the ratio of output collector current I_O, to the forward LED input current, I_F, times 100 percent.3/ I_F = 2 μA for channel under test. For all other channels, I_F = 10 mA.4/ Device considered a two-terminal device. Pins 1 through 8 are shorted together and pins 9 through 16 are shorted together.5/ Measured between the LED anode and cathode shorted together and pins 10 through 15 shorted together.6/ Parameters shall be tested as part of device initial characterization and after design and process changes. Parameters shall be guaranteed to the limits specified in table I for all lots not specifically tested.7/ CM_H is the maximum tolerable common mode transient to assure that the output will remain in a high logic state (i.e., V_O > 2.0 V).8/ In applications where dV/dt may exceed 50,000 V/μs (such as a static discharge) a series resistor, R_{CC}, should be included to protect the detector IC's from destructively high surge currents. The recommended value is:

$$R_{CC} = \frac{1 \text{ V}}{0.6 I_F (\text{mA})} \text{ k}\Omega$$

9/ CM_L is the maximum tolerable common mode transient to assure that the output will remain in a low logic state (i.e., V_O < 0.8 V).

**STANDARD
MICROCIRCUIT DRAWING**

DEFENSE SUPPLY CENTER COLUMBUS
COLUMBUS, OHIO 43218-3990


SIZE
A

REVISION LEVEL
K

83024

SHEET
6

Case outline X.



Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A		4.57		.180
A1	1.40	1.65	.055	.065
b	0.41	0.51	.016	.020
c	0.18	0.33	.007	.013
D	20.07	20.83	.790	.820
e	2.29	2.79	.090	.110
E	9.65	9.91	.380	.390
E1		8.13		.320
L	1.07	1.32	.042	.052
R	0.89	1.52	.035	.060


NOTES:

1. The U. S. Government preferred system of measurement is the metric SI. This item was designed using inch-pound units of measurement. In case of problems involving conflicts between the metric and inch-pound units, the inch-pound shall rule.
2. Pin 1 is indicated by a dot marked on top of the package.

FIGURE 1. Case outline(s).

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 7

Case outline Y.



Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A		4.32		.170
A1	1.14	1.40	.045	.055
b	0.41	0.51	.016	.020
c	0.18	0.33	.007	.013
D	20.07	20.83	.790	.820
e	2.29	2.79	.090	.110
eA	7.37	7.87	.290	.310
E		8.13		.320
Q	0.51		.020	
S	0.89	1.52	.035	.060


NOTES:

1. The U. S. Government preferred system of measurement is the metric SI. This item was designed using inch-pound units of measurement. In case of problems involving conflicts between the metric and inch-pound units, the inch-pound shall rule.
2. Pin 1 is indicated by a dot marked on top of the package.

FIGURE 1. Case outline(s) - Continued.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 8

Case outline Z.



Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A		3.56		.140
b	0.89	1.14	.035	.045
c	0.18	0.33	.007	.013
D	20.07	20.83	.790	.820
e	2.29	2.79	.090	.110
eA	7.37	7.87	.290	.310
E		8.13		.320
Q	0.51		.020	
S	0.89	1.52	.035	.060

NOTES:

1. The U. S. Government preferred system of measurement is the metric SI. This item was designed using inch-pound units of measurement. In case of problems involving conflicts between the metric and inch-pound units, the inch-pound shall rule.
2. Pin 1 is indicated by a dot marked on top of the package.

FIGURE 1. Case outline(s) - Continued.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 9

Device type	01
Case outlines	E, F, X, Y, and Z
Terminal number	Terminal symbol
1	Cathode 1
2	Anode 1
3	Anode 2
4	Cathode 2
5	Cathode 3
6	Anode 3
7	Anode 4
8	Cathode 4
9	NC
10	GND
11	Output 4
12	Output 3
13	Output 2
14	Output 1
15	V _{CC}
16	NC

FIGURE 2. Terminal connections.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 10

TABLE II. Electrical test requirements.

MIL-PRF-38534 test requirements	Subgroups (in accordance with MIL-PRF-38534, group A test table)
Interim electrical parameters	1
Final electrical parameters	1*, 2, 3, 9
Group A test requirements	1, 2, 3, 4, 9, 10, 11
Group C end-point electrical parameters	1, 2, 3
End-point electrical parameters for Radiation Hardness Assurance (RHA) devices	Not applicable

* PDA applies to subgroup 1.

4.3 Conformance and periodic inspections. Conformance inspection (CI) and periodic inspection (PI) shall be in accordance with MIL-PRF-38534 and as specified herein.

4.3.1 Group A inspection (CI). Group A inspection shall be in accordance with MIL-PRF-38534 and as follows:

- a. Tests shall be as specified in table II herein.
- b. Subgroups 5, 6, 7, and 8 shall be omitted.

4.3.2 Group B inspection (PI). Group B inspection shall be in accordance with MIL-PRF-38534.

4.3.3 Group C inspection (PI). Group C inspection shall be in accordance with MIL-PRF-38534 and as follows:

- a. End-point electrical parameters shall be as specified in table II herein.
- b. Steady-state life test, method 1005 of MIL-STD-883.
 - (1) Test condition A, B, C, or D. The test circuit shall be maintained by the manufacturer under document revision level control and shall be made available to either DSCC-VA or the acquiring activity upon request. Also, the test circuit shall specify the inputs, outputs, biases, and power dissipation, as applicable, in accordance with the intent specified in method 1005 of MIL-STD-883.
 - (2) T_A as specified in accordance with table I of method 1005 of MIL-STD-883.
 - (3) Test duration: 1,000 hours, except as permitted by method 1005 of MIL-STD-883.

4.3.4 Group D inspection (PI). Group D inspection shall be in accordance with MIL-PRF-38534.

4.3.5 Radiation Hardness Assurance (RHA) inspection. RHA inspection is not currently applicable to this drawing.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 11

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-PRF-38534.

6. NOTES

6.1 Intended use. Microcircuits conforming to this drawing are intended for use for Government microcircuit applications (original equipment), design applications, and logistics purposes.

6.2 Replaceability. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.

6.3 Configuration control of SMD's. All proposed changes to existing SMD's will be coordinated as specified in MIL-PRF-38534.

6.4 Record of users. Military and industrial users shall inform Defense Supply Center Columbus (DSCC) when a system application requires configuration control and the applicable SMD. DSCC will maintain a record of users and this list will be used for coordination and distribution of changes to the drawings. Users of drawings covering microelectronic devices (FSC 5962) should contact DSCC-VA, telephone (614) 692-1081.

6.5 Comments. Comments on this drawing should be directed to DSCC-VA, Columbus, Ohio 43218-3990, or telephone (614) 692-1081.

6.6 Sources of supply. Sources of supply are listed in MIL-HDBK-103 and QML-38534. The vendors listed in MIL-HDBK-103 and QML-38534 have submitted a certificate of compliance (see 3.7 herein) to DSCC-VA and have agreed to this drawing.

STANDARD MICROCIRCUIT DRAWING DEFENSE SUPPLY CENTER COLUMBUS COLUMBUS, OHIO 43218-3990	SIZE A		83024
		REVISION LEVEL K	SHEET 12

STANDARD MICROCIRCUIT DRAWING BULLETIN

DATE: 06-12-07

Approved sources of supply for SMD 83024 are listed below for immediate acquisition information only and shall be added to MIL-HDBK-103 and QML-38534 during the next revisions. MIL-HDBK-103 and QML-38534 will be revised to include the addition or deletion of sources. The vendors listed below have agreed to this drawing and a certificate of compliance has been submitted to and accepted by DSCC-VA. This information bulletin is superseded by the next dated revisions of MIL-HDBK-103 and QML-38534. DSCC maintains an online database of all current sources of supply at <http://www.dscclia.mil/Programs/Smcr/>.

Standard microcircuit drawing PIN <u>1/</u>	Vendor CAGE number	Vendor similar PIN <u>2/</u>
8302401EA 8302401EC 8302401EA 8302401EC	31757 31757 50434 50434	6N140A 6N140A 6N140A/883B#200 6N140A/883B
8302401FC	50434	HCPL-6751
8302401XA 8302401XA	31757 50434	6N140A 6N140A/883B#300
8302401YA 8302401YC	50434 50434	6N140A/883B#100 6N140A/883B#100
8302401ZA 8302401ZC	50434 50434	6N140A/883B#600 6N140A/883B#600

- 1/ The lead finish shown for each PIN representing a hermetic package is the most readily available from the manufacturer listed for that part. If the desired lead finish is not listed contact the Vendor to determine its availability.
- 2/ Caution. Do not use this number for item acquisition. Items acquired to this number may not satisfy the performance requirements of this drawing.

Vendor CAGE
numberVendor name
and address

31757

Micropac Industries, Incorporated
Optoelectronics Division
905 E. Walnut Street
Garland, TX 75040-6611

50434

Avago Technologies
350 West Trimble Road
San Jose, CA 95131

The information contained herein is disseminated for convenience only and the Government assumes no liability whatsoever for any inaccuracies in the information bulletin.