


© 2026 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E5	PART STATUS CHANGE TO DISCONTINUANCE	06JUL2026	NS	PS







796641-3 AS SHOWN



1. MATERIALS AND FINISH:
   HOUSING: PA 6-6, UL 94-V0, COLOR: BLACK.
   CLAMP: BRASS, NICKEL PLATED.
   DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, FINISH: SEE TABLE.
   CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
3. WIRE SIZE RANGE: 12-30 AWG.
4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677.
5. NOT CUMULATIVE TOLERANCE
6. BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL WHERE SPACE PERMITS.
7. INK MARKING: WHITE COLOR
   NUMERICAL SEQUENCE: FROM LEFT TO RIGHT.

CONTACT FINISH	MARKING	DIM L	NO OF POSN	PART NUMBER
OBSOLETE	.762µm GOLD		40.0	8	4-796641-4
TIN	SEE DETAIL T	25.0	5	4-796641-2
OBSOLETE	TIN	SEE DETAIL S	60.0	12	4-796641-1
OBSOLETE	TIN	SEE DETAIL R	50.0	10	4-796641-0
OBSOLETE	TIN	SEE DETAIL P	20.0	4	3-796641-9
OBSOLETE	TIN	SEE DETAIL N	40.0	8	3-796641-8
OBSOLETE	TIN	SEE DETAIL M	30.0	6	3-796641-6
TIN	SEE DETAIL L	10.0	2	3-796641-2
OBSOLETE	TIN		125.0	25	2-796641-5
TIN		120.0	24	2-796641-4
OBSOLETE	TIN		115.0	23	2-796641-3
OBSOLETE	TIN		110.0	22	2-796641-2
OBSOLETE	TIN		105.0	21	2-796641-1
TIN		100.0	20	2-796641-0
OBSOLETE	TIN		95.0	19	1-796641-9
TIN		90.0	18	1-796641-8
OBSOLETE	TIN		85.0	17	1-796641-7
TIN		80.0	16	1-796641-6
TIN		75.0	15	1-796641-5
OBSOLETE	TIN		70.0	14	1-796641-4
TIN		65.0	13	1-796641-3
TIN		60.0	12	1-796641-2
TIN		55.0	11	1-796641-1
TIN		50.0	10	1-796641-0
TIN		45.0	9	796641-9
TIN		40.0	8	796641-8
TIN		35.0	7	796641-7
TIN		30.0	6	796641-6
TIN		25.0	5	796641-5
TIN		20.0	4	796641-4
TIN		15.0	3	796641-3
TIN		10.0	2	796641-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL 1

FINISH 1

DWN S.WELDON 18OCT2000
CHK D.BIEVENOUR 18OCT2000
APVD D.BIEVENOUR 18OCT2000

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

TE Connectivity

NAME TERMI-BLOK PLUG, STACKING, 5.00mm PITCH
-


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-796641	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 2 | REV E5


Downloaded from Arrow.com.

© 2026 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




DETAIL L
SCALE 4:1 7




DETAIL M
SCALE 4:1 7




DETAIL P
SCALE 4:1 7




DETAIL T
SCALE 4:1 7



DETAIL N
SCALE 4:1 7



DETAIL R
SCALE 4:1 7



DETAIL S
SCALE 4:1 7

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL

FINISH

DWN S.WELDON 18OCT2000
CHK D.BIEVENOUR 18OCT2000
APVD D.BIEVENOUR 18OCT2000
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME TERMI-BLOK PLUG, STACKING, 5.00mm PITCH
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-796641	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 2 OF 2 | REV E5

Downloaded from Arrow.com.