





A	B	C	D	E	F	G	H
				REVISIONS			
	REV	DESCRIPTION, ECN, EAR NO.		DATE	APP'D		
	A	PROPOSAL		MAR09/18	L.CHAN		



RECOMMENDED PANEL CUTOUT




RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)


POSITION DIMENSIONS
ARE BASIC



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.



BI-COLOUR LED DETAIL
(RED/YELLOW AND GREEN/ORANGE
LED'S ARE ALSO AVAILABLE)



LED SCHEMATIC

MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0

CONTACTS: PHOSPHOR BRONZE
(FLAT) PLATING: 50 μ [1.27 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.

SHIELD: STAINLESS STEEL WITH TIN FINISH ON SOLDER TAILS

RECOMMENDED SOLDERING TEMPERATURE:
WAVE SOLDERING TEMPERATURE AT 260°C MAXIMUM
FOR 5 SEC MAXIMUM.

AMPHENOL PART NUMBER: RJHSE-NP8X-A1

REFER TO LED OPTIONS DRAWING
FOR ORDERING CODES

UNLESS SPECIFIED OTHERWISE	DRAWN	W.QIU	DATE
PRIMARY UNITS INCH	CHECKED	L.CHAN	MAR09/18
SECONDARY MILLIMETER	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE ± 0.025	ENG. REL. NO.		
2 DECIMAL PLACES ± 0.020	REF.		
3 DECIMAL PLACES ± 0.015	THIRD ANGLE PROJECTION		
ANGULAR DEGREES $\pm 1.0^\circ$	DO NOT SCALE DRAWING		
	CODE ID NO. 03554	DWG SIZE: C	SCALE: N/A
			Sheet 1 of 1

Amphenol Canada Corp.
www.amphenolcanada.com
TITLE VERTICAL SINGLE PORT MODULAR
JACK CONNECTOR, SHIELDED WITH LEDS
.130" LONG CONTACT TAILS- RoHS COMPLIANT
DWG. NO. P-RJHSE-NP8X-A1
REV A

