

PI2DPX2023A
1.8V 20Gbps DP 2.1 Linear ReDriver with AUX Listener & Pin Strap Control
Description

The PI2DPX2023A is a 20Gbps DP2.1 linear ReDriver™ in a 4-to-4 configuration operated by a 1.8V power supply. The device supports UHBR20 (20Gbps), UHBR13.5 (13.5Gbps), UHBR10 (10Gbps), HBR3 (8.1Gbps), HBR2 (5.4Gbps), HBR (2.7Gbps) and RBR (1.62Gbps) under various DisplayPort speeds. With the on-chip AUX channel listener, the device can automatically monitor the system operation status to enter D3 power saving mode.

The non-blocking linear ReDriver design ensures that the differential signals conveying pre-shoot and de-emphasis equalization waveforms from the transmitter side to the receiver side help optimize the overall channel link adjustment conducted by the system transmitter and receiver that has been equipped with DFE. The CTLE equalizers are implemented at the inputs of the ReDriver to compensate the channel loss and reduce the ISI jitters. The flat gain adjustments support the eye diagram opening. The CTLE EQ gains and flat gains are tuned via pin strap control.

Application(s)

- Graphics Add-In Cards
- Laptop, Desktop and AIO PCs
- Workstations and Servers
- Docking Stations
- Display Monitors
- Gaming Consoles
- Active Cables

Features

- 4-to-4 Linear ReDriver Channel Configuration with CTLE Gain Compensation Up to 9.6dB @20Gbps
- Supports 4-Lane DP2.1 (UHBR20/UHBR13/UHBR10)/HBR3/HBR2/HBR/RBR
- Ultra Low Latency (<300ps) for Better Interoperability and Data Throughput
- 4 Level Controls on CTLE Gain (2.8 to 9.6dB), Flat Gain (-4 to +2dB)
- Integrated AUX Channel Listener for D3 Power Saving Mode
- Low Active Current Consumption
 - 4-lane DP: 160mA (typical)
- Supports DisplayPort Dual Mode
- Single Power Supply: 1.8V +/-5%
- Industrial Temperature Support: -40°C to +85°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.
- Packaging (Pb-free & Green):
 - Tiny 32-pin, WLGA (FLA) 2.85 x 4.5 mm (0.4 mm pitch, 0.7mm max height)

Ordering Information

Orderable Part Number	Package Code	Package Description
PI2DPX2023AFLAEX	FLA	32-Pin, W-LGA4528-32

Notes:

- E = Pb-free and Green
- X suffix = Tape/Reel

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

PI2DPX2023A

Document Number DS46347 Rev 2-2