



Part Number : [1120955127](#)
Product Description : Brad EtherNet/IP CIP Safety HarshIO Modules, Classic 60.00mm, IP67, 8 Ports M12, 12 PNP Safety Inputs, 4 Sourcing Safety Outputs, M8 Memory Key, 4-Pole Power
Series Number : 112095
Status : Active
Product Category : Industrial I/O Modules
Engineering Number : TCDEC-8B4P-DYU-G8



Documents & Resources

[TCDEC-8B4x-DxU-GxView software](#)
3D Models and Design Files
[3D Model 1120955127_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 7(c)-I; 6(c); 7(a); 6(a)-I per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Industrial I/O Modules
Series	112095
Description	Brad EtherNet/IP CIP Safety HarshIO Modules, Classic 60.00mm, IP67, 8 Ports M12, 12 PNP Safety Inputs, 4 Sourcing Safety Outputs, M8 Memory Key, 4-Pole Power
Application	Filling and Packaging Machines, Machine Tool Industry, Material Handling Systems
Approvals	CE, UL, cUL, TÜV, ODVA
Comments	12 safe inputs + 4 safe outputs, Cat 4 / PLe, M8 memory key
EPLAN	Yes
IP Rating	IP67
Product Family	IP67-Rated HarshIO Modules
Product Name	HarshIO EtherNet/IP,IP CIP Safety
Protocol	EtherNet/IP CIP Safety
UPC	889056265188

Electrical

Current - Maximum Output	1.0A per Channel
EMC	EN 62061:2005+AC:2010+A1:2013, IEC 61131-2:2007
Input Delay	ON – OFF, OFF – ON
Input Device Supply	700mA per port
Input Type	PNP or Dry Contact

Physical

Bus Input	4-pole Micro-Change (M12), D-Coded, Female
Bus Output	4-pole Ultra-Lock (M12), D-Coded, Female
Format	Classic (60mm)
Housing Width	60.00mm
I/O Connector	5-pole Ultra-Lock (M12), A-Coded, Female
I/O Ports	8x M12
I/O Signal Mix	12 input / 4 output
Mechanical Shock	15G, 11ms, 3 AXIS
Net Weight	1054.148/g
Power Input	4-pole Mini-Change
Power Output	4-pole Mini-Change
Temperature Range - Operating	-25°C to +70°C
Vibration	50G, 6ms, 3 AXIS

This document was generated on Sep 12, 2023
