

# Datasheet for part number DB-25S-A191-A197

|                                                                              |
|------------------------------------------------------------------------------|
| Our Catalog Part Number: DB-25S-A191-A197                                    |
| Our Global Manufacturing Part Number: 121073-2307 D                          |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: ORIGINAL D |

| Product Datasheet               |                                        |
|---------------------------------|----------------------------------------|
| General                         | Standard D-Subminiature                |
| Wire Gauge Range AWG            | AWG 20-28                              |
| Mating Cycles                   | 200                                    |
| Dielectric Withstanding Voltage | 1200 VAC at sea level                  |
| Current Rating                  | 7.5 A at 85°C / 5 A at 105°C           |
| Contact Resistance              | 10 milli Ohm max                       |
| Operating Temperature           | -55°/+125°                             |
| Salt Spray Test                 | 20 hours                               |
| Shell Material                  | steel                                  |
| Shell Finish                    | tin                                    |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0       |
| Insulator Color                 | black                                  |
| Contact Arrangement             | 25 contacts size 20                    |
| Gender                          | Socket                                 |
| Contact Type                    | turned                                 |
| Contact Material                | copper alloy                           |
| Contact Finish                  | gold over nickel (Performance Class 2) |
| Contact Termination             | Solder Pot                             |
| Mounting Methode                | .120" (3,05mm) Through Hole            |

Specifications and dimensions subject to change.