





NOTES: (UNLESS OTHERWISE SPECIFIED)

- MATERIAL:
SHELL: THERMOPLASTIC, UL94 V-0.
INSERT: THERMOPLASTIC, UL94 V-0.
COUPLING NUT: THERMOPLASTIC, UL94 V-0.
O-RING: NBR OR SILICONE RUBBER.
WASHER: SILICONE RUBBER.
BACK SHELL: THERMOPLASTIC, UL94 V-0.
CLAMP NUT: THERMOPLASTIC, UL94 V-0.
CLAMP RING: THERMOPLASTIC, UL94 V-0.
CABLE SEAL: EPDM.
- SPECIFICATIONS:
2.1 RATED CURRENT: 45A (MAX).
2.2 RATED VOLTAGE: 600V(AC/DC).
2.3 OPERATING TEMPERATURE: SEE TABLE.
2.4 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE@2500 VOLTS AC.
2.5 INSULATION RESISTANCE: 5000 MEGOHMS MIN.
2.6 IP CLASS: IP67 AND IP69K IN THE MATED CONDITION, WIRE SEALS FULLY POPULATED.
2.7 MATING CYCLES DURABILITY: 500 CYCLES MIN.
2.8 RoHS COMPLIANT.
- SUITABLE CONTACTS : 8# CONTACT.

A4	CONTACT SIZE	CONTACT PN	WIRE RANGE
	8#	MS10A23x-25	16 - 14AWG
		MS10A23x-63	12 - 10AWG
		MS10A23x-10	8 AWG

- IN THE CONTACT PN,"x" DENOTE DIFFERENT PLATING.
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASED DRAWING	Nov-10-17	Nick	TOMMY
A2	--	UPDATE CABLE OD RANGE	Feb-07-2018	Nick	TOMMY
A3	--	UPDATE DRAWING	Mar-26-2018	White	Tommy
A4	--	UPDATE NOTES	Oct-18-2018	Blink	Tommy

DIMENSION ØA	CABLE OD RANGE
12.3MM	6.0-12.0MM
14.3MM	9.0-14.0MM

KEY	PART NUMBER	
	-40°C ~ +105°C	-40°C ~ +125°C
N	RTS6BS14N3S	RTS6BS14N3S03

QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference =			
SIGNATURES		DATE	Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036 ECO-MATE, PLUG, BACK SHELL, SIZE 14,3POS, SOCKET SIZE B TYPE C- DWG NO: RTS6BS14*3Sxx REVISION A4 SCALE: NONE SHEET 1 OF 1
DRAWN: Blink		Oct-18-2018	
CHECKED: Tod		Oct-18-2018	
ENGINEER:			
APPROVAL: Tommy		Oct-18-2018	
CUSTOMER:			
MATERIAL SPECIFICATIONS:			
PROCESS SPECIFICATIONS:			
NEXT ASSY:			

TITLE: ECO-MATE, PLUG, BACK SHELL, SIZE 14,3POS, SOCKET
DWG NO: RTS6BS14*3Sxx
REV: A4
SH: 1
OF: 1

ecomate® RM, RSSM and Aquarius™ Series
Size 3.6mm Contact & Tooling Options (1403 Insert Arrangement)

Machined, Crimp Contacts						
Part Number		Contact Size (AWG)	Wire Range (mm²)	Male Contact For Use w End Cap	Female Contact For Use w End Cap	Plating
Male	Female					
MP10A23T-10	MS10A23T-10	8AWG	10.0 mm²	No	No	Tin
MP10A23S-10	MS10A23S-10	8AWG	10.0 mm²	No	No	Silver
MP10A23F-10	MS10A23F-10	8AWG	10.0 mm²	No	No	Gold Flash
MP10A23G5-10	MS10A23G5-10	8AWG	10.0 mm²	No	No	Gold 5µ"
MP10A23G10-10	MS10A23G10-10	8AWG	10.0 mm²	No	No	Gold 10µ"
MP10A23G15-10	MS10A23G15-10	8AWG	10.0 mm²	No	No	Gold 15µ"
MP10A23G30-10	MS10A23G30-10	8AWG	10.0 mm²	No	No	Gold 30µ"
MP10A23S-63	MS10A23S-63	10-12AWG	4.0-6.0 mm²	No	No	Silver
MP10A23F-63	MS10A23F-63	10-12AWG	4.0-6.0 mm²	No	No	Gold Flash
MP10A23S-63	MS10A23S-63W	10-12AWG	4.0-6.0 mm²	No	Yes	Silver
MP10A23F-63	MS10A23F-63W	10-12AWG	4.0-6.0 mm²	No	Yes	Gold Flash
MP10A23TL	MS10A23T	10-12AWG	3.0-6.0 mm²	Yes	Yes	Tin
MP10A23SL	MS10A23S	10-12AWG	3.0-6.0 mm²	Yes	Yes	Silver
MP10A23FL	MS10A23F	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold Flash
MP10A23G5L	MS10A23G5	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 5µ"
MP10A23G10L	MS10A23G10	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 10µ"
MP10A23G15L	MS10A23G15	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 15µ"
MP10A23G30L	MS10A23G30	10-12AWG	3.0-6.0 mm²	Yes	Yes	Gold 30µ"
MP10A23S-25	MS10A23S-25	14-16AWG	1.5-2.5 mm²	No	No	Silver
MP10A23F-25	MS10A23F-25	14-16AWG	1.5-2.5 mm²	No	No	Gold Flash
MP10A23S-25	MS10A23S-25W	14-16AWG	1.5-2.5 mm²	No	Yes	Silver
MP10A23F-25	MS10A23F-25W	14-16AWG	1.5-2.5 mm²	No	Yes	Gold Flash

Machined, Tooling	
Part Number	Description
QXRT08	Contact Extraction Tool, # 8 (Ø 3.6mm) Contact
M300BT	Hand Crimper
WA27-300BT-EP	Pneumatic Crimper
TP968	Locator M3200BT and WA27-300BT-EP

Plating Options	
Symbol	Plating
T	Tin Plated (for Stamped & Formed Contacts)
S	Silver Plated 5Um (for Machined Contacts)
F	Gold Plated
G5	Gold Plated (Thickness 5µ")
G10	Gold Plated (Thickness 10µ")
G15	Gold Plated (Thickness 15µ")
G30	Gold Plated (Thickness 30µ")