




PRODUCT NUMBER


PITCH

YK211xx0x0J0G

6.35mm



RECOMMENDED P.C.B LAYOUT TOP VIEW



MATERIALS & ELECTRICAL

RATED VOLTAGE & CURRENT:

WITHSTAND VOLTAGE:

INSULATION RESISTANCE:

OPERATING TEMPERATURE RANG:

SCREW TORQUE VALUE:

WIRE RANGE:

1) HOUSING:

2) TERMINAL:

3) TERMINAL SCREWS:

APPROVAL: cus

300 V, 10 A

AC 2000 V/Min

1000 MΩ OR MORE AT DC 500 V

-40 °C ~ +115 °C

6.5 Lb-In.

22 - 16AWG

THERMOPLASTICS, UL 94 V-0 BLACK

BRASS, 0.8t

STEEL, M3

DIMENSION

Dim A	N×6.35+1.4
Dim B	(N-1)×6.35

N=Number of poles

Tolerance	Dim A	Dim B
2p-8p	±0.35	±0.25
9p-16p	±0.45	±0.35
17p-24p	±0.55	±0.45
25p-30p	±0.65	±0.55

PART NO.: YK 211xx 0 x 0 J0G

No. of poles
02 2 poles
03 3 poles
...
30 30 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface	tolerance	projection	product family	
ltr	ecn	no	dr	date	ASME Y14.5	ASME Y14.5	TERMINAL BLOCK	
					tolerances unless otherwise specified		title	
					angles	X.±0.5	TERMINAL BLOCK	
					holes	X.X±0.3	BARRIER TYPE	
					X'±1"	X.XX±0.1	scale	
					dr	EVAN LU 061114	dwg no	
					enr	EVAN LU 061114	sheet 1 of 1	
					chr	HANKE FENG 061114	size	
					appd	SHI JUN 061114	A4	
sheet index				revision	A		type	
				sheet	1		CUSTOMER Drawing	