molex



Part Number : 757145001
Product Description : Small Form-factor Pluggable (SFP) Stacked 2-by-2 Multi-Port Connector with 4 Lightpipes, with Press-fit PC Tails, 80 Circuits, Lead-Free
Series Number : 75714
Status : Active
Product Category : High-Speed I/O Connectors

Documents and Resources

Drawings

757145001_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-75310-001-001.pdf

AS-76090-001-001.pdf

PK-75714-001-001.pdf

PS-75310-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Connectors
Series	75714
Description	Small Form-factor Pluggable (SFP) Stacked 2-by-2 Multi-Port Connector with 4 Lightpipes, with Press-fit PC Tails, 80 Circuits, Lead-Free
Application	Module-to-Board
Comments	With 4 Lightpipes
Component Type	Receptacle
Product Name	SFP
Type	Pluggable
UPC	822350235457

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.5A

Downloaded from Arrow.com.

Data Rate	10.0 Gbps
Shielded	Yes
Shield Type	EMI Fingers
Voltage - Maximum	30V

Physical

Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black, Clear (Blue Tint)
Durability (mating cycles max)	200
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	52.522/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm
PC Tail Length	3.05mm
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

Solder Process Data

Downloaded from Arrow.com.

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
Stacked Multi-Port Insertion Tool, 2 by 2	622029970
Stacked Multi-Port Extraction Tool, 2 by 2	622029975
Stacked Multi-Port Connector Tooling	622030160

Downloaded from Arrow.com.