FO-52847-F

REV	DOCUMENT	CHANGED BY	CHECK
A	0005622	RJ 25MAY04	AK





CIRCUIT DIAGRAM



CHARACTERISTICS	
OPERATING TORQUE	4 IN LBS MAX
FULL TRAVEL TORQUE	4 IN LBS MAX
PRETRAVEL	5° MAX
TOTAL TRAVEL	75° REF
DIFFERENTIAL TRAVEL	5° MAX
OVERTRAVEL	70° MIN

CONTACT ARRANGMENT S P D T		
VOLTS	AMPS RESISTIVE	AMPS INDUCTIVE
125 VDC	2.0	1.0
250 VDC	0.7	0.4
120 VAC	20.0	20.0
240 VAC	15.0	15.0
480 VAC	10.0	10.0
600 VAC	5.0	5.0

NOTES
1 - SWITCH USES FLUROSILICONE SEALS IN OPERATING HEAD ONLY
2 - SWITCH CAVITY EPOXY FILLED

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: [X] US(inch) CUSTOMARY [ ] SI(mm) METRIC

NO PLACE	X	±.040	±1
ONE PLACE	.X	±.030	±0,4
TWO PLACE	.XX	±.015	±0,15
THREE PLACE	.XXX	±.005	±
ANGLES		±	±

RAW MATERIAL-COMMERCIAL STANDARD

THIRD ANGLE PROJECTION

DRAWN	R J	25MAY04
CHECK	A K	25MAY04

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED

2D PTC | ASME Y14.5M-1994

Honeywell

TITLE: SWITCH, ENCLOSED

SIZE	DWG TYPE	DRAWING NAME	REV
C	I	LSQYUB3K339	A

SCALE FULL | WEIGHT | SHEET 1 OF 1

Downloaded from Arrow.com.