FLYER

EX Series

0.8mm Pitch / 280pos.

Connectors for Medical and Industrial Applications

Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.



Shield | Multiple Position | Wide Variation


Features

1. **Optimum for portable ultrasound scanning interface**
2. **High pin count, yet small size and light weight**
3. **Enhanced grounding design**
4. **4-step displaced contact point for lower insertion force with high pin count**
5. **Floating locator improves mounting efficiency**

Wide Variations


[Plug on Probe Side]

Right Angle




[Receptacle on Device Side]


Right Angle




Straight



Shielded Type





M3 screws are not included.

*Dimensions are in millimeters

[Guides] Attachable with screwdriver

Guide Socket
Flathead / Cross Slot Screwdriver



Guide Pin
Nut Screwdriver



Guides can be attached to either plug or receptacle.
Hirose recommends attaching guide sockets to probe side and guide pins to device side.

Specifications

Rated Current	0.5A
Rated Voltage	250V AC
Contact Resistance	125mΩ Max. (100mA)
Insulation Resistance	250MΩ Min. (100V DC)
Withstanding Voltage	400V AC for 1 min.
Operating Temperature	-25 to 85ºC
Mating Durability	10,000 times

- RoHS compliant, Halogen-free product*

*This product satisfies halogen free requirements defined as 900 ppm maximum chlorine, 900 maximum bromine, and 1500 ppm maximum total of chlorine and bromine.

© 2020 HIROSE ELECTRIC CO., LTD. All rights reserved. Specifications herein are subject to change without notice. Contact Hirose for latest specifications, drawings, or availabilities.

Downloaded from Arrow.com.