

Memory Module Specifications

KSM32SED8/16MR

16GB 2Rx8 2G x 72-Bit PC4-3200

CL22 260-Pin ECC SODIMM

DESCRIPTION

Kingston's KSM32SED8/16MR is a 2G x 72-bit (16GB) DDR4-3200 CL22 SDRAM (Synchronous DRAM) w/ parity, 2Rx8, ECC, memory module, based on eighteen 1G x 8-bit FBGA components. The SPD is programmed to JEDEC standard latency DDR4-3200 timing of 22-22-22 at 1.2V. Each 260-pin SODIMM uses gold contact fingers. The electrical and mechanical specifications are as follows:

FEATURES

- Power Supply: VDD = 1.2V
- VDDQ = 1.2V
- VPP = 2.5V
- VDDSPD = 2.20V to 3.60V
- Functionality and operations comply with the DDR4 SDRAM datasheet
- 16 internal banks
- Bank Grouping is applied, and CAS to CAS latency (tCCD_L, tCCD_S) for the banks in the same or different bank group accesses are available
- Data transfer rates: PC4-3200, PC4-2933, PC4-2666, PC4-2400, PC4-2133, PC4-1866, PC4-1600
- Bi-Directional Differential Data Strobe
- 8 bit pre-fetch
- Burst Length (BL) switch on-the-fly BL8 or BC4(Burst Chop)
- Supports ECC error correction and detection
- On-Die Termination (ODT)
- Temperature sensor with integrated SPD
- This product is in compliance with the RoHS directive.
- Per DRAM Addressability is supported
- Internal Vref DQ level generation is available
- Write CRC is supported at all speed grades
- CA parity (Command/Address Parity) mode is supported
- RoHS Compliant and Halogen-Free

SPECIFICATIONS

CL(IDD)	22 cycles
Row Cycle Time (tRCmin)	45.75ns(min.)
Refresh to Active/Refresh Command Time (tRFCmin)	350ns(min.)
Row Active Time (tRASmin)	32ns(min.)
Maximum Operating Power	*
UL Rating	94 V - 0
Operating Temperature	0° C to +85° C
Storage Temperature	-55° C to +100° C

*See IDD Specifications (page 2)

Module Assembly




DRAM: MICRON (R-DIE)

Continued >>

IDD Specifications

Symbol	3200	Units
I_{DD0}	774	mA
I_{PP0}	54	mA
I_{DD1}	837	mA
I_{DD2N}	684	mA
I_{DD2NT}	711	mA
I_{DD2P}	540	mA
I_{DD2Q}	612	mA
I_{DD3N}	774	mA
I_{PP3N}	54	mA
I_{DD3P}	594	mA
I_{DD4R}	1449	mA
I_{DD4W}	1296	mA
I_{DD5R}	765	mA
I_{PP5R}	63	mA
I_{DD6N}	576	mA
I_{DD6E}	936	mA
I_{DD6R}	342	mA
I_{DD6A}	144	mA
I_{DD6A}	342	mA
I_{DD6A}	522	mA
I_{DD6A}	90	mA
I_{PP6X}	1737	mA
I_{DD7}	144	mA
I_{PP7}	432	mA
I_{DD8}	864	mA

MODULE DIMENSIONS



The product images shown are for illustration purposes only and may not be an exact representation of the product.
Kingston reserves the right to change any information at anytime without notice.