

DIN-Signal 40A FE contact solder Mflat



Image is for illustration purposes only. Please refer to product description.

Part number	09 03 000 6225
Specification	DIN-Signal 40A FE contact solder Mflat
HARTING eCatalogue	https://harting.com/09030006225

Identification

Category	Contacts
Series	DIN 41612 har-modular®
Type of contact	PCB solder contact
Description of the contact	Straight
Contacts for	DIN 41612 Type M-flat har-modular® M-flat module, female, straight

Version

Gender	Female contact for female connectors
Connection type	Motherboard to daughtercard Mezzanine PCB to cable
Manufacturing process	Turned contacts

Technical characteristics

Rated current	≤40 A
Insertion force	≤10 N
Withdrawal force	≥1.6 N
Performance level	1
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side

Page 1 / 3 | Creation date 2026-03-06 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com



Pushing Performance
Since 1945

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	no requirements (flammable mass < 10g)

Specifications and approvals

Specifications	DIN 41626
----------------	-----------

Commercial data

Packaging size	100
Net weight	1.045 g
Country of origin	Hungary
European customs tariff number	85366990
GTIN	5713140004115
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522



Pushing Performance
Since 1945

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques acc. to IEC 60512-5-2

