

SMBJE

600 W Transient voltage suppressor



Product features

- Low profile SMB package
- Excellent clamping capability
- 600 W peak pulse power capability at 10/1000 μ s waveform
- Typical I_R less than 1 μ A above 10 V
- Fast response time: typically less than 1.0 ps from 0 V to V_{BR} minimum
- High temperature reflow soldering: +260 °C /40 s at terminal
- Plastic package meets UL 94 V-0 flammability rating
- Meets moisture sensitivity level (MSL) level 1
- Terminal: Solder plated leads, solderable per J-STD-002
- For surface mounted applications in order to optimize board space
- UL 497B recognized.
File No. : E198449 Guide QVGQ2

Applications

- Consumer electronics
- Telecommunications
- Computing and servers
- Appliances
- Industrial automation
- Mobile and wearables

Environmental compliance and general specifications





Ordering part number

SMBJE 5-0 C A

Family name _____
 V_R voltage _____
 ("-" indicates decimal point) _____
 Bi-/Uni-Directional _____
 (Blank=Uni, C=Bi)
 Voltage tolerance _____

PIN configuration



Powering Business Worldwide


Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
Storage operating junction temperature range	T_{STG}/T_J	-55 to +150	°C
Steady state power dissipation at $T_L = +75$ °C	$P_{M(AV)}$	5.0	W
Peak pulse power dissipation on 10/1000 μ s waveform	P_{PP}	600	W
Maximum instantaneous forward voltage at 100 A for unidirectional	V_F	5.0	V
Peak forward surge current, 8.3 ms single half sine wave ¹	I_{FSM}	100	A
Typical thermal resistance junction to lead	$R_{\theta JL}$	20	°C/W
Typical thermal resistance junction to ambient	$R_{\theta JA}$	100	°C/W

1. Measured on 8.3 ms single half sine wave or equivalent square wave for unidirectional device only, duty cycle = 4 per minute maximum

Mechanical parameters, pad layout- mm



Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	3.30	3.94	0.130	0.155
B	4.30	4.80	0.169	0.189
C	1.90	2.20	0.075	0.087
D	0.95	1.52	0.037	0.060
E	5.20	5.60	0.205	0.220
F	0.051	0.203	0.002	0.008
G	0.15	0.31	0.006	0.012
H	2.10	2.40	0.083	0.094
J	2.20		0.087	
K		2.60		0.102
L	2.30		0.091	

Part marking




Cathode band (Uni-polar only)

Part marking: xxxx = Date code
yy- Refer to marking designator listed in Electrical Characteristics table

Packaging information (mm)

Drawing not to scale.

Supplied in tape and reel packaging, 3,000 parts per 13" diameter reel (EIA-481 compliant)



Dimension	Millimeters	Inches
A0	3.76 ± 0.3	0.148 ± 0.012
B0	5.69 ± 0.3	0.224 ± 0.012
C	330.0	13.0
D0	1.55 ± 0.1	0.061 ± 0.004
E	1.75 ± 0.2	0.069 ± 0.008
E1	13.3 ± 0.3	0.524 ± 0.012
F	5.50 ± 0.2	0.217 ± 0.008
P0	4.00 ± 0.2	0.157 ± 0.008
P1	8.00 ± 0.2	0.3145 ± 0.008
P2	2.00 ± 0.2	0.079 ± 0.008
W	12.0 ± 0.2	0.472 ± 0.008
W1	15.7 ± 2.0	0.618 ± 0.079

SMBJE

600 W Transient voltage suppressor


Technical Data 11214
Effective November 2020

Electrical characteristics (+25 °C)


Part number		Marking		V_R	$I_R @ V_R$	$V_{BR} @ I_T$		I_T	$V_C @ I_{PP}$	I_{PP}
Uni-polar	Bi-polar	Uni	Bi	(V)	(μ A)	min (V)	max (V)	(mA)	max (V)	(A)
SMBJE5-0A	SMBJE5-0CA	KE	AE	5	120	6.4	7	10	9.2	65.2
SMBJE6-0A	SMBJE6-0CA	KG	AG	6	120	6.67	7.37	10	10.3	58.3
SMBJE6-5A	SMBJE6-5CA	KK	AK	6.5	120	7.22	7.98	10	11.2	53.6
SMBJE7-0A	SMBJE7-0CA	KM	AM	7	50	7.78	8.6	10	12	50
SMBJE7-5A	SMBJE7-5CA	KP	AP	7.5	50	8.33	9.21	1	12.9	46.5
SMBJE8-0A	SMBJE8-0CA	KR	AR	8	20	8.89	9.83	1	13.6	44.1
SMBJE8-5A	SMBJE8-5CA	KT	AT	8.5	10	9.44	10.4	1	14.4	41.7
SMBJE9-0A	SMBJE9-0CA	KV	AV	9	5	10	11.1	1	15.4	39
SMBJE10A	SMBJE10CA	KX	AX	10	2	11.1	12.3	1	17	35.3
SMBJE11A	SMBJE11CA	KZ	AZ	11	1	12.2	13.5	1	18.2	33
SMBJE12A	SMBJE12CA	LE	BE	12	1	13.3	14.7	1	19.9	30.2
SMBJE13A	SMBJE13CA	LG	BG	13	1	14.4	15.9	1	21.5	27.9
SMBJE14A	SMBJE14CA	LK	BK	14	1	15.6	17.2	1	23.2	25.9
SMBJE15A	SMBJE15CA	LM	BM	15	1	16.7	18.5	1	24.4	24.6
SMBJE16A	SMBJE16CA	LP	BP	16	1	17.8	19.7	1	26	23.1
SMBJE17A	SMBJE17CA	LR	BR	17	1	18.9	20.9	1	27.6	21.8
SMBJE18A	SMBJE18CA	LT	BT	18	1	20	22.1	1	29.2	20.6
SMBJE20A	SMBJE20CA	LV	BV	20	1	22.2	24.5	1	32.4	18.6
SMBJE22A	SMBJE22CA	LX	BX	22	1	24.4	26.9	1	35.5	16.9
SMBJE24A	SMBJE24CA	LZ	BZ	24	1	26.7	29.5	1	38.9	15.4
SMBJE26A	SMBJE26CA	ME	CE	26	1	28.9	31.9	1	42.1	14.3
SMBJE28A	SMBJE28CA	MG	CG	28	1	31.1	34.4	1	45.4	13.2
SMBJE30A	SMBJE30CA	MK	CK	30	1	33.3	36.8	1	48.4	12.4
SMBJE33A	SMBJE33CA	MM	CM	33	1	36.7	40.6	1	53.3	11.3
SMBJE36A	SMBJE36CA	MP	CP	36	1	40	44.2	1	58.1	10.4
SMBJE40A	SMBJE40CA	MR	CR	40	1	44.4	49.1	1	64.5	9.3
SMBJE43A	SMBJE43CA	MT	CT	43	1	47.8	52.8	1	69.4	8.7
SMBJE45A	SMBJE45CA	MV	CV	45	1	50	55.3	1	72.7	8.3
SMBJE48A	SMBJE48CA	MX	CX	48	1	53.3	58.9	1	77.4	7.8
SMBJE51A	SMBJE51CA	MZ	CZ	51	1	56.7	62.7	1	82.4	7.3
SMBJE54A	SMBJE54CA	NE	DE	54	1	60	66.3	1	87.1	6.9
SMBJE58A	SMBJE58CA	NG	DG	58	1	64.4	71.2	1	93.6	6.4
SMBJE60A	SMBJE60CA	NK	DK	60	1	66.7	73.7	1	96.8	6.2
SMBJE64A	SMBJE64CA	NM	DM	64	1	71.1	78.6	1	103	5.8
SMBJE70A	SMBJE70CA	NP	DP	70	1	77.8	86	1	113	5.3
SMBJE75A	SMBJE75CA	NR	DR	75	1	83.3	92.1	1	121	5
SMBJE78A	SMBJE78CA	NT	DT	78	1	86.7	95.8	1	126	4.8
SMBJE85A	SMBJE85CA	NV	DV	85	1	94.4	104	1	137	4.4
SMBJE90A	SMBJE90CA	NX	DX	90	1	100	111	1	146	4.1
SMBJE100A	SMBJE100CA	NZ	DZ	100	1	111	123	1	162	3.7
SMBJE110A	SMBJE110CA	PE	EE	110	1	122	135	1	177	3.4
SMBJE120A	SMBJE120CA	PG	EG	120	1	133	147	1	193	3.1
SMBJE130A	SMBJE130CA	PK	EK	130	1	144	159	1	209	2.9
SMBJE150A	SMBJE150CA	PM	EM	150	1	167	185	1	243	2.5
SMBJE160A	SMBJE160CA	PP	EP	160	1	178	197	1	259	2.3
SMBJE170A	SMBJE170CA	PR	ER	170	1	189	209	1	275	2.2
SMBJE180A	SMBJE180CA	PT	ET	180	1	201	222	1	292	2.1
SMBJE190A	SMBJE190CA	PV	EV	190	1	211	234	1	307	2
SMBJE200A	SMBJE200CA	PX	EX	200	1	224	247	1	324	1.9
SMBJE210A	SMBJE210CA	PZ	EZ	210	1	233	258	1	337	1.8
SMBJE220A	SMBJE220CA	QE	FE	220	1	246	272	1	356	1.7
SMBJE250A	SMBJE250CA	QG	FG	250	1	279	309	1	405	1.5
SMBJE300A	SMBJE300CA	QK	FK	300	1	335	371	1	486	1.3
SMBJE350A	SMBJE350CA	QM	FM	350	1	391	432	1	567	1.1
SMBJE400A	SMBJE400CA	QP	FP	400	1	447	494	1	648	0.9
SMBJE440A	SMBJE440CA	QR	FR	440	1	492	543	1	713	0.8

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

V- I curve characteristics (Uni-directional)



V- I curve characteristics (Bi-directional)



Surge waveform: 10/1000 μ s

V_R : Stand-off voltage – Maximum voltage that can be applied

V_{BR} : Breakdown voltage


V_C : Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}

I_R : Reverse leakage current


I_T : Test current

V_F : Forward voltage drop for Uni-directional TVS diode


Pulse waveform



Pulse derating curve



Peak pulse power dissipation vs. pulse width



Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-180 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	40 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2020 Eaton
All Rights Reserved
Printed in USA
Publication No. 11214 BU-MC20192
November 2020

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

