

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image









In some applications it is useful to protect the feed through connection with a separate fuse. Fuse terminal blocks are made up of one terminal block bottom section with a fuse insertion carrier. The fuses vary from pivoting fuse levers and pluggable fuse holders to screwable closures and flat plug-in fuses.

General ordering data

Fuse terminal, Screw connection, black, 4 mm², 10 A, 36 V, Number of connections: 2, Number of levels: 1, TS 35, TS 32
<u>1880410000</u>
WSI 4/2/LD 10-36V AC/DC
4032248541935
25 ST



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Appro	vals
-------	------

Approvals	C € ∰ 71	us Page 1

ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	E60693

Dimensions and weights

Depth	53.5 mm	Depth (inches)	2.1063 inch
Height	81.6 mm	Height (inches)	3.2126 inch
Width	9.1 mm	Width (inches)	0.3583 inch
Net weight	22.8 g		

Temperatures

Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%

Material data

Material	Wemid	Colour	black
UL 94 flammability rating	V-0		

System specifications

Version	Screw connection, Fuse isolator, with LED, One end without connector	End cover plate required	Yes
Number of potentials	1	Number of levels	1
Number of clamping points per level	2	Number of potentials per tier	1
Levels cross-connected internally	No	PE connection	No
Rail	TS 35, TS 32	N-function	No
PE function	No	PEN function	No

2 clampable conductors (H05V/H07V) with equal cross-section (rated connection)

Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, max.	1.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, 2 clampable wires, min.	0.5 mm ²
Wire cross-section, finely stranded, two clampable wires, max.	1.5 mm ²	Wire connection cross section, finely stranded, two clampable wires, min.	0.5 mm ²

Additional technical data

Open sides	right	Number of similar terminals	1	
Type of mounting	Snap-on			

Creation date 05.07.2025 04:54:49 MEZ

Catalogue status / Drawings 2



Weidmüller Interface GmbH & Co. KG

 $1.5\ mm^2$

min.

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

CSA rating data	CSA	rating	data
-----------------	------------	--------	------

Wire cross section max. (CSA)	10 AWG	Certificate No. (CSA)	200039-1575489
Wire cross section min. (CSA)	30 AWG		

Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A3		
Wire connection cross section AWG,	AWG 10		
max.			
Connection direction	on side		
Fightening torque, max.	0.8 Nm		
Fightening torque, min.	0.5 Nm		
Stripping length	10 mm		
Type of connection 2	Screw connection		
Type of connection	Screw connection		
Number of connections	2		
Clamping range, max.	6 mm ²		
Clamping range, min.	0.5 mm ²		
Clamping screw	M 3		
Blade size	0.6 x 3.5 mm		
Wire connection cross section AWG, min.	AWG 22		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	4 mm ²		
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²		
Wire connection cross section, finely stranded, max.	6 mm ²		
Wire connection cross section, finely stranded, min.	0.5 mm ²		
Connection cross-section, stranded, max.	6 mm ²		
Connection cross-section, stranded, mi	n. 1.5 mm²		
Torque level with DMS electric screwdriver	2		
Wire connection cross-section, solid core, max.	6 mm²		
Wire connection cross-section, solid core, min.	0.5 mm ²		
Clampable conductor	Connection specification	Screw connection	
	Cross-section for conductor connection	Туре	solid, H05(07) V-U
		min.	0.5 mm ²
		max.	6 mm ²
		nominal	4 mm ²
	wire end ferrule	Stripping length	min. 11 mm
			max. 11 mm
			nominal 11 mm
		Tightening torque	min. 0.5 Nm
			max. 0.8 Nm
	Connection specification	Screw connection	I .
	Cross-section for conductor connection	Туре	stranded, H07V-R
	Sisse sestion for conductor conficction	- / F -	1 F2



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

	max.	6 mm ²	
	nominal	4 mm ²	
wire end ferrule	Stripping length	min.	11 mm
		max.	11 mm
		nominal	11 mm
	Tightening torque	min.	0.5 Nm
		max.	0.8 Nm
Connection specification	Screw connection		
Cross-section for conductor connection	Туре	flexible, H05(07) V-K	
	min.	0.5 mm ²	
	max.	6 mm ²	
	nominal	4 mm ²	
wire end ferrule	Stripping length	min.	11 mm
		max.	11 mm
		nominal	11 mm
	Tightening torque	min.	0.5 Nm
		max.	0.8 Nm

Dimensions

Display element

Type of voltage for indicator	AC/DC	Operating voltage for display, min.	10 V

Fuse terminals

Cartridge fuse	6.3 x 32 mm (1/4 x 1 1/4")	Fuse holder (cartridge holder)	Pivoting
Type of voltage for indicator	AC/DC	Display	Red LED
Operating voltage, max.	36 V	Power loss for short-circuit protection only for a composite arrangement	2.5 W at 2.5 A @ 68°C
Power loss for short-circuit protection only for an individual arrangement	4.0 W at 10 A @ 55°C	Power loss, 1-pole; 2-pole; 3-pole	
Permitted power loss for fuse with semiconductor protection		Power loss for overload and short-circui protection for a composite arrangement	_

General

Wire connection cross section AWG,	AWG 10	Wire connection cross section AWG,	AWG 22
max.		min.	
Standards	IEC 60947-7-3	Rail	TS 35, TS 32

Rating data

Rated cross-section	4 mm ²	Rated voltage	36 V
Rated voltage to adjoining terminal	500 V	Rated DC voltage	36 V
Rated current	10 A	Current at maximum wires	10 A
Standards	IEC 60947-7-3	Volume resistance according to IEC 60947-7-x	1 mΩ
Rated impulse withstand voltage	6 V	Power loss in accordance with IEC 60947-7-x	1.02 W





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Ш	rating	data
UL	Iaum	uata

Conductor size Factory wiring max. 10 AWG (cURus)	Certificate No. (cURus)	E60693
Conductor size Field wiring min. (cURus) 30 AWG	Conductor size Factory wiring min. (cURus)	30 AWG
Conductor size Field wiring max (cLIRus)10 AWG		

Important note

Product information	The voltage depends on the selected fuse element or the selected indicator light

Classifications

EC000899	ETIM 7.0	EC000899
EC000899	ETIM 9.0	EC000899
EC000899	ECLASS 9.0	27-14-11-16
27-14-11-16	ECLASS 10.0	27-14-11-16
27-14-11-16	ECLASS 12.0	27-14-11-16
27-25-01-13	ECLASS 14.0	27-25-01-13
27-25-01-13		
	EC000899 EC000899 27-14-11-16 27-14-11-16 27-25-01-13	EC000899 ETIM 9.0 EC000899 ECLASS 9.0 27-14-11-16 ECLASS 10.0 27-14-11-16 ECLASS 12.0 27-25-01-13 ECLASS 14.0






Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

4 mm²

4

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

General ordering data

Type WAP WSI4/2
Order No. 1880450000
GTIN (EAN) 4032248541911
Oty. 50 ST

Version
End plate for terminals, black, Height: 71.12 mm, Width: 2.5 mm, V-0,

Wemid, Snap-on: No

Combined screwing and cutting tool "Swifty®"

Combined cutting/screwing tool: Swifty® and Swifty® set for clean cutting of copper cables up to 1.5 mm² (solid) and 2.5 mm² (flexible)



General ordering data

Type SWIFTY CUT AND STRIP SET Version

Order No. 9006060000 Cutting and screwing-tool, Cutting tool for one-hand operation

GTIN (EAN) 4032248257638

Oty. 1 ST

Slotted screwdriver



Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

General ordering data

1 ST

 Type
 SDS 0.6X3.5X100
 Version

 Order No.
 9008330000
 Screwdriver, Screwdriver

 GTIN (EAN)
 4032248056286

Creation date 05.07.2025 04:54:49 MEZ

Qty.



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/5 MC NE WS
Order No.	1609801044
GTIN (EAN)	4008190397111
Otv	1000 ST

Version

Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00

Weidmueller, white

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

Туре	BZT 1 WS 10/5	Version
Order No.	<u>1805490000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Туре	BZT 1 ZA WS 10/5	Version
Order No.	<u>1805520000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 ST	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Z-Series

Series

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Туре Order No. 1269070000 GTIN (EAN)

Qty.

4050118094091

25 ST

Version

Accessories, Accessories holder