



YAG8CLTC14LD

by Burndy
Catalog ID: YAG8CLTC14LD

Prop 65 Notice

Cu terminal,#8flex 23 navy,1/4 stud,49 die index

Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Barrel, Lead Plated
UPC	781810034576
UPC 12 Digit	7818100345766

Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.52 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	34 mm
Dimension - Length Overall inch	1.32 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.44 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.33 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	#8
Conductor - Copper DLO Size Range	8 (37/#24) DLO
Conductor - Copper Flex G Size	#8 AWG
Conductor - Copper Flex G Size Range	8 AWG
Conductor - Copper Flex H Size	#8 AWG
Conductor - Copper Flex H Size Range	8 AWG
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex I Size Range	8 AWG
Conductor - Copper Flex K Size	#8 AWG
Conductor - Copper Flex K Size Range	8 AWG
Conductor - Copper Flex M Size	8 AWG
Conductor - Copper Flex M Size Range	8 AWG
Conductor - Copper Str Navy Size	23 Navy
Conductor - Copper Str Size	8 AWG
Conductor - CopperWeld C Solid Size	8 AWG
Conductor - CopperWeld Solid Size Range	8 AWG
Conductor - CopperWeld Str Size	8 A AWG;8 C AWG;8 D AWG
Conductor - CopperWeld Str Size Range	8 A AWG-8 D AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	200
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)