





4611110016009



接线图

Wiring Diagram



励磁顺序 vs. 旋转方向

Exciting Sequence vs. Direction of Rotation

STEP	A	B	C	D	O	M	CCW
1	-	-	-	-	+	+	↑
2	-	-	-	-	+	+	
3	-	-	-	-	+	+	
4	-	-	-	-	+	+	

从安装面看为顺时针方向

Clockwise view from mounting side

规格 Specifications

1. 相数 Number of Phase	4
2. 步距角 Step Angle	1.8°
3. 额定电压 Rated Voltage	7.52 V
4. 额定电流 Rated Current	0.47 Amp
5. 保持力矩 Holding Torque	0.2 Nm Typ.(Two phase on/rated current)
6. 相电阻 Phase Resistance	16 Ω±10%(20°C)
7. 相电感 Phase Inductance	8.5 mH±20%(1kHz 1V rms)
8. 转子惯量 Rotor Inertia	38 gcm ²
9. 电机重量 Motor Weight	0.21kg
10. 绝缘等级 Insulation Class	B(130°C)

铭牌 Label Detail

MOONS' STEPPING MOTOR

TYPE 17HD0050-15

XXXXXXXX YY/MM/DD

Work Order

加工单号

Date Format

日期格式

保 密

Unit: mm

第一角画法


FIRST ANGLE METHOD

未注线性与角度尺寸公差
Tolerances for linear and angular dimensions without
individual tolerance indications

GB/T 1804-m eqv ISO 2768-1 : m

未注形状与位置尺寸公差
Geometrical tolerance for features without
individual tolerance indications

GB/T 1184-K eqv ISO 2768-2 : K



批准 Approve

标准化 Standard

工艺 Technology

审核 Check

设计 Design

10.19

10.19

10.19

10.19

2016.10.18

NAMES

SIGNATURE

DATE

MOONS'

Shanghai Moons' Electric Co., Ltd.

This document is released for information only. Its reproduction in whole or in part or its dissemination to third parties is prohibited. All trademarks and registered trademarks appearing on this document are the property of their respective owners.

Type: 17HD0050-15

Rev.B

SCALE 1:1

Sheet 1 of 1

REV.

版本记录 REVISION RECORD

DATE

UNLESS OTHERWISE SPECIFIED

1

2

3

4

5

6

7

8