

PJC7400

30V N-Channel Enhancement Mode MOSFET


Voltage 30 V **Current** 1.9A

Features

- $R_{DS(ON)}$, $V_{GS}@10V$, $I_D@1.9A < 70m\Omega$
- $R_{DS(ON)}$, $V_{GS}@4.5V$, $I_D@1.6A < 75m\Omega$
- $R_{DS(ON)}$, $V_{GS}@2.5V$, $I_D@1.2A < 85m\Omega$
- $R_{DS(ON)}$, $V_{GS}@1.8V$, $I_D@0.7A < 110m\Omega$
- Advanced Trench Process Technology
- Specially Designed for Switch Load, PWM Application, etc.
- Lead free in comply with EU RoHS 2011/65/EU directives.
- Green molding compound as per IEC61249 Std.
(Halogen Free)

Mechanical Data

- Case: SOT-323 Package
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.00018 ounces, 0.005 grams
- Marking: C00



Maximum Ratings and Thermal Characteristics ($T_A=25^{\circ}C$ unless otherwise noted)

PARAMETER		SYMBOL	LIMIT	UNITS
Drain-Source Voltage		V _{DS}	30	V
Gate-Source Voltage		V _{GS}	±12	V
Continuous Drain Current		I _D	1.9	A
Pulsed Drain Current		I _{DM}	7.6	A
Power Dissipation	T _a =25°C	P _D	350	mW
	Derate above 25°C		2.8	mW/°C
Operating Junction and Storage Temperature Range		T _J ,T _{STG}	-55~150	°C
Typical Thermal resistance		R _{θJA}	357	°C/W
- Junction to Ambient ^(Note 3)				



PJC7400

Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)







PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNITS
Static						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =250uA	30	-	-	V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250uA	0.4	0.72	1.2	V
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} =10V, I _D =1.9A	-	58	70	mΩ
		V _{GS} =4.5V, I _D =1.6A	-	61	75	
		V _{GS} =2.5V, I _D =1.2A	-	69	85	
		V _{GS} =1.8V, I _D =0.7A	-	80	110	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V, V _{GS} =0V	-	0.01	1	uA
Gate-Source Leakage Current	I _{GSS}	V _{GS} =±12V, V _{DS} =0V	-	±10	±100	nA
Dynamic						
Total Gate Charge	Q _g	V _{DS} =15V, I _D =1.9A, V _{GS} =10V ^(Note 1,2)	-	4.8	-	nC
Gate-Source Charge	Q _{gs}		-	0.5	-	
Gate-Drain Charge	Q _{gd}		-	0.7	-	
Input Capacitance	C _{iss}	V _{DS} =15V, V _{GS} =0V, f=1.0MHZ	-	447	-	pF
Output Capacitance	C _{oss}		-	34	-	
Reverse Transfer Capacitance	C _{rss}		-	22	-	
Switching						
Turn-On Delay Time	td _(on)	V _{DD} =15V, I _D =1.9A, V _{GS} =10V, R _G =6Ω ^(Note 1,2)	-	2	-	ns
Turn-On Rise Time	tr			38	-	
Turn-Off Delay Time	td _(off)			812	-	
Turn-Off Fall Time	tf			64	-	
Drain-Source Diode						
Maximum Continuous Drain-Source Diode Forward Current	I _S	---	-	-	0.5	A
Diode Forward Voltage	V _{SD}	I _S =1.0A, V _{GS} =0V		0.77	1.2	V

NOTES :

1. Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$
2. Essentially independent of operating temperature typical characteristics.
3. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins mounted on a 1 inch FR-4 with 2oz. square pad of copper
4. The maximum current rating is package limited

PJC7400

TYPICAL CHARACTERISTIC CURVES





PJC7400

TYPICAL CHARACTERISTIC CURVES




Fig.7 Gate-Charge Characteristics




Fig.8 Threshold Voltage Variation with Temperature.





Fig.9 Capacitance vs. Drain-Source Voltage.

PJC7400

PART NO PACKING CODE VERSION

Part No Packing Code	Package Type	Packing type	Marking	Version
PJC7400_R1_00001	SOT-323	3K pcs / 7" reel	C00	Halogen free
PJC7400_R2_00001	SOT-323	12K pcs / 13" reel	C00	Halogen free

MOUNTING PAD LAYOUT





PJC7400

Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.